

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P136093

Luminaire Tested: **LD6A30D010TE ERW6A30930 6LW1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P136093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23358)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A30D010TE ERW6A30930 6LW1LI
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2710.7 lumens
Efficiency: N/A
Efficacy: 59.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.12
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 45.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P136093

CATALOG NUMBER: LD6A30D010TE ERW6A30930 6LW1LI

Luminous Intensity Polar Plot





TEST NUMBER: P136093

CATALOG NUMBER: LD6A30D010TE ERW6A30930 6LW1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65	65	65	65
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59	59	59	59
7	79	68	62	57	77	68	61	57	66	61	57	65	60	56	64	59	56	54	54	54	54
8	74	64	57	53	73	63	57	52	62	56	52	61	56	52	60	55	52	50	50	50	50
9	70	60	53	49	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113904
5°	116808
10°	124776
15°	134733
20°	136925
25°	128537
30°	113203
35°	92204
40°	66966
45°	42967
50°	22583
55°	7712
60°	2218
65°	571
70°	362
75°	479
80°	0
85°	0



TEST NUMBER: P136093

CATALOG NUMBER: LD6A30D010TE ERW6A30930 6LW1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.5	6.4
10°-20°	559.6	20.6
20°-30°	811.9	30.0
30°-40°	715.2	26.4
40°-50°	366.2	13.5
50°-60°	77.1	2.8
60°-70°	6.0	0.2
70°-80°	1.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1545.0	57.0
0°-40°	2260.2	83.4
0°-60°	2703.5	99.7
0°-90°	2710.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2710.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1746	
5°	1784	174
15°	1995	560
25°	1786	812
35°	1158	715
45°	466	366
55°	68	77
65°	4	6
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P136093

CATALOG NUMBER: LD6A30D010TE ERW6A30930 6LW1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1745.9
2.5°	1749.7
5°	1783.6
7.5°	1830.7
10°	1883.5
12.5°	1943.9
15°	1994.8
17.5°	2008.0
20°	1972.2
22.5°	1893.0
25°	1785.6
27.5°	1655.5
30°	1502.7
32.5°	1334.9
35°	1157.7
37.5°	972.9
40°	786.3
42.5°	618.5
45°	465.7
47.5°	333.7
50°	222.5
52.5°	130.1
55°	67.8
57.5°	34.0
60°	17.0
62.5°	7.6
65°	3.7
67.5°	3.7
70°	1.9
72.5°	1.9
75°	1.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)