

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684428

Luminaire Tested: **LX6C55D010 EX6C559040 6LBNH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684428  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C55D010 EX6C559040 6LBNH  
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 6LBN TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3851.0 lumens  
Efficiency: N/A  
Efficacy: 60.3 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 63.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684428

CATALOG NUMBER: LX6C55D010 EX6C559040 6LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P684428

CATALOG NUMBER: LX6C55D010 EX6C559040 6LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	270625
5°	263927
10°	243533
15°	215609
20°	187208
25°	160128
30°	132014
35°	86933
40°	46730
45°	20692
50°	8392
55°	6050
60°	3848
65°	2750
70°	2260
75°	1504
80°	2241
85°	0



TEST NUMBER: P684428

CATALOG NUMBER: LX6C55D010 EX6C559040 6LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	443.9	11.5
10°-20°	1058.6	27.5
20°-30°	1212.8	31.5
30°-40°	814.8	21.2
40°-50°	232.8	6.0
50°-60°	57.0	1.5
60°-70°	21.7	0.6
70°-80°	8.4	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2715.4	70.5
0°-40°	3530.2	91.7
0°-60°	3820.0	99.2
0°-90°	3851.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3851.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4937	
5°	4796	444
15°	3799	1059
25°	2647	1213
35°	1299	815
45°	267	233
55°	63	57
65°	21	22
75°	7	8
85°	0	1
90°	0	



TEST NUMBER: P684428

CATALOG NUMBER: LX6C55D010 EX6C559040 6LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4936.6
2.5°	4901.5
5°	4796.1
7.5°	4606.4
10°	4374.9
12.5°	4079.7
15°	3799.0
17.5°	3504.1
20°	3209.0
22.5°	2928.3
25°	2647.3
27.5°	2387.5
30°	2085.5
32.5°	1685.2
35°	1299.0
37.5°	947.9
40°	653.0
42.5°	428.3
45°	266.9
47.5°	161.4
50°	98.4
52.5°	77.2
55°	63.3
57.5°	49.2
60°	35.1
62.5°	28.0
65°	21.2
67.5°	14.1
70°	14.1
72.5°	7.1
75°	7.1
77.5°	7.1
80°	7.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)