

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685111

Luminaire Tested: **LX6C55D010 EX6559050 6LRMDLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C55D010 EX6559050 6LRMDLI
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4689.0 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685111
CATALOG NUMBER: LX6C55D010 EX6559050 6LRMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P685111

CATALOG NUMBER: LX6C55D010 EX6559050 6LRMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	383939
5°	384679
10°	366599
15°	315660
20°	260043
25°	203111
30°	146687
35°	75121
40°	36633
45°	15219
50°	2772
55°	1615
60°	1053
65°	778
70°	577
75°	508
80°	379
85°	0



TEST NUMBER: P685111

CATALOG NUMBER: LX6C55D010 EX6559050 6LRMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	655.2	14.0
10°-20°	1541.6	32.9
20°-30°	1526.8	32.6
30°-40°	774.0	16.5
40°-50°	166.7	3.6
50°-60°	15.9	0.3
60°-70°	6.1	0.1
70°-80°	2.2	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3723.6	79.4
0°-40°	4497.6	95.9
0°-60°	4680.2	99.8
0°-90°	4689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4689.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7004	
5°	6990	655
15°	5562	1542
25°	3358	1527
35°	1122	774
45°	196	167
55°	17	16
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P685111

CATALOG NUMBER: LX6C55D010 EX6559050 6LRMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7003.6
2.5°	7012.0
5°	6990.4
7.5°	6880.8
10°	6585.7
12.5°	6111.1
15°	5561.9
17.5°	4999.5
20°	4457.5
22.5°	3915.5
25°	3357.9
27.5°	2789.4
30°	2317.3
32.5°	1784.9
35°	1122.5
37.5°	755.2
40°	511.9
42.5°	331.2
45°	196.3
47.5°	87.9
50°	32.5
52.5°	21.7
55°	16.9
57.5°	12.0
60°	9.6
62.5°	7.2
65°	6.0
67.5°	4.8
70°	3.6
72.5°	2.4
75°	2.4
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)