

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P135251

Luminaire Tested: **LD6A30D010TE ERN6A30840 6LN1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P135251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23370)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A30D010TE ERN6A30840 6LN1H
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 4000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2548.1 lumens
Efficiency: N/A
Efficacy: 56.1 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.84
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 45.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P135251

CATALOG NUMBER: LD6A30D010TE ERN6A30840 6LN1H

Luminous Intensity Polar Plot





TEST NUMBER: P135251

CATALOG NUMBER: LD6A30D010TE ERN6A30840 6LN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70			
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54			
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219254
5°	212089
10°	189082
15°	164809
20°	142722
25°	122461
30°	102792
35°	72134
40°	37550
45°	17872
50°	9378
55°	5084
60°	3497
65°	2300
70°	1698
75°	1512
80°	1127
85°	0



TEST NUMBER: P135251

CATALOG NUMBER: LD6A30D010TE ERN6A30840 6LN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.5	11.6
10°-20°	681.8	26.8
20°-30°	780.2	30.6
30°-40°	555.8	21.8
40°-50°	168.1	6.6
50°-60°	43.6	1.7
60°-70°	16.2	0.6
70°-80°	5.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1758.5	69.0
0°-40°	2314.3	90.8
0°-60°	2526.0	99.1
0°-90°	2548.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2548.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3361	
5°	3238	297
15°	2440	682
25°	1701	780
35°	906	556
45°	194	168
55°	45	44
65°	15	16
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P135251

CATALOG NUMBER: LD6A30D010TE ERN6A30840 6LN1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3360.7
2.5°	3321.9
5°	3238.5
7.5°	3071.7
10°	2854.2
12.5°	2636.7
15°	2440.1
17.5°	2249.4
20°	2055.7
22.5°	1874.0
25°	1701.2
27.5°	1537.3
30°	1364.5
32.5°	1156.0
35°	905.7
37.5°	649.5
40°	440.9
42.5°	292.0
45°	193.7
47.5°	134.1
50°	92.4
52.5°	59.6
55°	44.7
57.5°	32.8
60°	26.8
62.5°	20.9
65°	14.9
67.5°	11.9
70°	8.9
72.5°	6.0
75°	6.0
77.5°	3.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)