

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563972

Luminaire Tested: **LX6C55D010 EX6C559030 6LBSH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P563972  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C55D010 EX6C559030 6LBSH  
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6387.9 lumens  
Efficiency: N/A  
Efficacy: 100.0 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 63.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563972

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P563972

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	183149
5°	182296
10°	178532
15°	172044
20°	164129
25°	155283
30°	146472
35°	137915
40°	129865
45°	121051
50°	110376
55°	97478
60°	82504
65°	64780
70°	46226
75°	25311
80°	4451
85°	0



TEST NUMBER: P563972

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	312.9	4.9
10°-20°	850.5	13.3
20°-30°	1181.2	18.5
30°-40°	1289.0	20.2
40°-50°	1202.4	18.8
50°-60°	912.7	14.3
60°-70°	499.7	7.8
70°-80°	137.5	2.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2344.7	36.7
0°-40°	3633.7	56.9
0°-60°	5748.8	90.0
0°-90°	6387.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6387.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3341	
5°	3313	313
15°	3031	851
25°	2567	1181
35°	2061	1289
45°	1561	1202
55°	1020	913
65°	499	500
75°	120	138
85°	0	2
90°	0	



TEST NUMBER: P563972

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3340.9
2.5°	3340.9
5°	3312.7
7.5°	3270.5
10°	3207.2
12.5°	3122.8
15°	3031.4
17.5°	2918.9
20°	2813.4
22.5°	2686.7
25°	2567.2
27.5°	2447.7
30°	2313.9
32.5°	2187.3
35°	2060.8
37.5°	1934.2
40°	1814.7
42.5°	1688.0
45°	1561.4
47.5°	1434.8
50°	1294.2
52.5°	1160.5
55°	1019.9
57.5°	886.2
60°	752.5
62.5°	619.0
65°	499.4
67.5°	386.7
70°	288.4
72.5°	196.9
75°	119.5
77.5°	56.4
80°	14.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)