

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684453

Luminaire Tested: **LX6C60D010 EX6C609030 6LBNH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684453
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C60D010 EX6C609030 6LBNH
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4099.0 lumens
Efficiency: N/A
Efficacy: 56.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684453

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P684453

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	288053
5°	280926
10°	259214
15°	229491
20°	199266
25°	170435
30°	140515
35°	92535
40°	49743
45°	22026
50°	8929
55°	6442
60°	4090
65°	2932
70°	2404
75°	1589
80°	2368
85°	0



TEST NUMBER: P684453

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.5	11.5
10°-20°	1126.8	27.5
20°-30°	1290.9	31.5
30°-40°	867.3	21.2
40°-50°	247.8	6.0
50°-60°	60.7	1.5
60°-70°	23.1	0.6
70°-80°	8.9	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2890.2	70.5
0°-40°	3757.5	91.7
0°-60°	4066.0	99.2
0°-90°	4099.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4099.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5254	
5°	5105	473
15°	4044	1127
25°	2818	1291
35°	1383	867
45°	284	248
55°	67	61
65°	23	23
75°	8	9
85°	0	1
90°	0	



TEST NUMBER: P684453

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5254.5
2.5°	5217.2
5°	5105.0
7.5°	4903.1
10°	4656.6
12.5°	4342.5
15°	4043.6
17.5°	3729.8
20°	3415.7
22.5°	3116.8
25°	2817.7
27.5°	2541.2
30°	2219.8
32.5°	1793.7
35°	1382.7
37.5°	1009.0
40°	695.1
42.5°	455.9
45°	284.1
47.5°	171.8
50°	104.7
52.5°	82.2
55°	67.4
57.5°	52.4
60°	37.3
62.5°	29.8
65°	22.6
67.5°	15.0
70°	15.0
72.5°	7.5
75°	7.5
77.5°	7.5
80°	7.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)