

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685128

Luminaire Tested: **LX6C60D010 EX6609040 6LBNLI**

Issue Date: 2/14/2022

Test Information

Test Method: LM-79-08
Report Number: P685128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C60D010 EX6609040 6LBNLI
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5262.9 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685128

CATALOG NUMBER: LX6C60D010 EX6609040 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685128

CATALOG NUMBER: LX6C60D010 EX6609040 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	656888
5°	614301
10°	501009
15°	368680
20°	254116
25°	188654
30°	141705
35°	88365
40°	42895
45°	14715
50°	1927
55°	1462
60°	833
65°	986
70°	1218
75°	0
80°	0
85°	0



TEST NUMBER: P685128

CATALOG NUMBER: LX6C60D010 EX6609040 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	996.3	18.9
10°-20°	1788.2	34.0
20°-30°	1445.8	27.5
30°-40°	832.9	15.8
40°-50°	176.1	3.3
50°-60°	15.2	0.3
60°-70°	7.5	0.1
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4230.3	80.4
0°-40°	5063.2	96.2
0°-60°	5254.4	99.8
0°-90°	5262.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5262.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11983	
5°	11163	996
15°	6496	1788
25°	3119	1446
35°	1320	833
45°	190	176
55°	15	15
65°	8	8
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685128

CATALOG NUMBER: LX6C60D010 EX6609040 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11982.6
2.5°	11838.6
5°	11163.1
7.5°	10191.8
10°	9000.3
12.5°	7778.6
15°	6496.1
17.5°	5259.1
20°	4355.9
22.5°	3665.4
25°	3118.9
27.5°	2656.1
30°	2238.6
32.5°	1775.8
35°	1320.4
37.5°	918.2
40°	599.4
42.5°	364.3
45°	189.8
47.5°	75.8
50°	22.6
52.5°	22.6
55°	15.3
57.5°	15.3
60°	7.6
62.5°	7.6
65°	7.6
67.5°	7.6
70°	7.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)