

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684467

Luminaire Tested: **LX6C60D010 EX6C609040 6LBNH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684467
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C60D010 EX6C609040 6LBNH
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4163.0 lumens
Efficiency: N/A
Efficacy: 57.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684467

CATALOG NUMBER: LX6C60D010 EX6C609040 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P684467

CATALOG NUMBER: LX6C60D010 EX6C609040 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	292548
5°	285312
10°	263261
15°	233077
20°	202376
25°	173097
30°	142712
35°	93980
40°	50523
45°	22367
50°	9066
55°	6537
60°	4155
65°	2970
70°	2452
75°	1610
80°	2399
85°	0



TEST NUMBER: P684467

CATALOG NUMBER: LX6C60D010 EX6C609040 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	479.9	11.5
10°-20°	1144.4	27.5
20°-30°	1311.0	31.5
30°-40°	880.9	21.2
40°-50°	251.7	6.0
50°-60°	61.6	1.5
60°-70°	23.4	0.6
70°-80°	9.0	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2935.4	70.5
0°-40°	3816.2	91.7
0°-60°	4129.5	99.2
0°-90°	4163.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4163.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5336	
5°	5185	480
15°	4107	1144
25°	2862	1311
35°	1404	881
45°	288	252
55°	68	62
65°	23	23
75°	8	9
85°	0	1
90°	0	



TEST NUMBER: P684467

CATALOG NUMBER: LX6C60D010 EX6C609040 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5336.5
2.5°	5298.6
5°	5184.7
7.5°	4979.6
10°	4729.3
12.5°	4410.3
15°	4106.8
17.5°	3788.0
20°	3469.0
22.5°	3165.5
25°	2861.7
27.5°	2580.9
30°	2254.5
32.5°	1821.7
35°	1404.3
37.5°	1024.7
40°	706.0
42.5°	463.0
45°	288.5
47.5°	174.5
50°	106.3
52.5°	83.4
55°	68.4
57.5°	53.2
60°	37.9
62.5°	30.3
65°	22.9
67.5°	15.3
70°	15.3
72.5°	7.6
75°	7.6
77.5°	7.6
80°	7.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)