

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685167

Luminaire Tested: **LX6C70D010 EX6709030 6LBMLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685167
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C70D010 EX6709030 6LBMLI
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6407.0 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685167

CATALOG NUMBER: LX6C70D010 EX6709030 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P685167

CATALOG NUMBER: LX6C70D010 EX6709030 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	439548
5°	435372
10°	412551
15°	374559
20°	330977
25°	286142
30°	223674
35°	137166
40°	70403
45°	27972
50°	9083
55°	3125
60°	2686
65°	2140
70°	1330
75°	1758
80°	0
85°	0



TEST NUMBER: P685167

CATALOG NUMBER: LX6C70D010 EX6709030 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	738.6	11.5
10°-20°	1838.9	28.7
20°-30°	2137.7	33.4
30°-40°	1309.0	20.4
40°-50°	325.1	5.1
50°-60°	38.0	0.6
60°-70°	14.2	0.2
70°-80°	5.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4715.3	73.6
0°-40°	6024.3	94.0
0°-60°	6387.4	99.7
0°-90°	6407.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6407.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8018	
5°	7912	739
15°	6600	1839
25°	4731	2138
35°	2050	1309
45°	361	325
55°	33	38
65°	16	14
75°	8	5
85°	0	0
90°	0	



TEST NUMBER: P685167

CATALOG NUMBER: LX6C70D010 EX6709030 6LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8018.0
2.5°	8009.8
5°	7911.6
7.5°	7698.3
10°	7411.2
12.5°	7034.2
15°	6599.7
17.5°	6132.4
20°	5673.4
22.5°	5214.1
25°	4730.6
27.5°	4173.0
30°	3533.5
32.5°	2787.4
35°	2049.6
37.5°	1442.8
40°	983.8
42.5°	614.8
45°	360.8
47.5°	205.0
50°	106.5
52.5°	49.3
55°	32.7
57.5°	24.5
60°	24.5
62.5°	16.5
65°	16.5
67.5°	8.3
70°	8.3
72.5°	8.3
75°	8.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)