

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685173

Luminaire Tested: **LX6C70D010 EX6709035 6LBNLI**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P685173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C70D010 EX6709035 6LBNLI
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5774.0 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685173
CATALOG NUMBER: LX6C70D010 EX6709035 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685173

CATALOG NUMBER: LX6C70D010 EX6709035 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	720666
5°	673947
10°	549656
15°	404475
20°	278788
25°	206970
30°	155467
35°	96945
40°	47060
45°	16141
50°	2115
55°	1606
60°	921
65°	1090
70°	1346
75°	0
80°	0
85°	0



TEST NUMBER: P685173

CATALOG NUMBER: LX6C70D010 EX6709035 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1093.0	18.9
10°-20°	1961.9	34.0
20°-30°	1586.2	27.5
30°-40°	913.7	15.8
40°-50°	193.2	3.3
50°-60°	16.7	0.3
60°-70°	8.3	0.1
70°-80°	1.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4641.0	80.4
0°-40°	5554.8	96.2
0°-60°	5764.6	99.8
0°-90°	5774.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5774.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13146	
5°	12247	###
15°	7127	1962
25°	3422	1586
35°	1449	914
45°	208	193
55°	17	17
65°	8	8
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685173

CATALOG NUMBER: LX6C70D010 EX6709035 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13146.0
2.5°	12988.1
5°	12247.0
7.5°	11181.3
10°	9874.2
12.5°	8533.9
15°	7126.8
17.5°	5769.7
20°	4778.8
22.5°	4021.3
25°	3421.7
27.5°	2914.0
30°	2456.0
32.5°	1948.3
35°	1448.6
37.5°	1007.3
40°	657.6
42.5°	399.7
45°	208.2
47.5°	83.2
50°	24.8
52.5°	24.8
55°	16.8
57.5°	16.8
60°	8.4
62.5°	8.4
65°	8.4
67.5°	8.4
70°	8.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)