

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684538

Luminaire Tested: **LX6C70D010 EX6C709035 6LBNH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684538
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C70D010 EX6C709035 6LBNH
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4567.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684538

CATALOG NUMBER: LX6C70D010 EX6C709035 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P684538

CATALOG NUMBER: LX6C70D010 EX6C709035 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	320939
5°	312997
10°	288811
15°	255694
20°	222013
25°	189900
30°	156562
35°	103102
40°	55425
45°	24537
50°	9953
55°	7178
60°	4561
65°	3256
70°	2693
75°	1779
80°	2652
85°	0



TEST NUMBER: P684538

CATALOG NUMBER: LX6C70D010 EX6C709035 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	526.5	11.5
10°-20°	1255.5	27.5
20°-30°	1438.3	31.5
30°-40°	966.4	21.2
40°-50°	276.1	6.0
50°-60°	67.6	1.5
60°-70°	25.7	0.6
70°-80°	10.0	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3220.2	70.5
0°-40°	4186.6	91.7
0°-60°	4530.2	99.2
0°-90°	4567.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4567.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5854	
5°	5688	526
15°	4505	1255
25°	3140	1438
35°	1541	966
45°	316	276
55°	75	68
65°	25	26
75°	8	10
85°	0	1
90°	0	



TEST NUMBER: P684538

CATALOG NUMBER: LX6C70D010 EX6C709035 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5854.4
2.5°	5812.9
5°	5687.8
7.5°	5462.9
10°	5188.3
12.5°	4838.3
15°	4505.3
17.5°	4155.6
20°	3805.6
22.5°	3472.7
25°	3139.5
27.5°	2831.3
30°	2473.3
32.5°	1998.5
35°	1540.6
37.5°	1124.2
40°	774.5
42.5°	507.9
45°	316.5
47.5°	191.4
50°	116.7
52.5°	91.5
55°	75.1
57.5°	58.3
60°	41.6
62.5°	33.2
65°	25.1
67.5°	16.8
70°	16.8
72.5°	8.4
75°	8.4
77.5°	8.4
80°	8.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)