

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685177

Luminaire Tested: **LX6C70D010 EX6709040 6LBMLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C70D010 EX6709040 6LBMLI
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6507.0 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685177
CATALOG NUMBER: LX6C70D010 EX6709040 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P685177

CATALOG NUMBER: LX6C70D010 EX6709040 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94	94	94	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82	82	82	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76	76	76	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71	71	71	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67	67	67	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63	63	63	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	446412
5°	442163
10°	418991
15°	380405
20°	336146
25°	290605
30°	227162
35°	139307
40°	71505
45°	28406
50°	9228
55°	3183
60°	2730
65°	2179
70°	1346
75°	1779
80°	0
85°	0



TEST NUMBER: P685177

CATALOG NUMBER: LX6C70D010 EX6709040 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	750.2	11.5
10°-20°	1867.6	28.7
20°-30°	2171.1	33.4
30°-40°	1329.5	20.4
40°-50°	330.1	5.1
50°-60°	38.6	0.6
60°-70°	14.4	0.2
70°-80°	5.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4788.9	73.6
0°-40°	6118.4	94.0
0°-60°	6487.1	99.7
0°-90°	6507.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6507.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8143	
5°	8035	750
15°	6703	1868
25°	4804	2171
35°	2082	1329
45°	366	330
55°	33	39
65°	17	14
75°	8	6
85°	0	0
90°	0	



TEST NUMBER: P685177

CATALOG NUMBER: LX6C70D010 EX6709040 6LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8143.2
2.5°	8134.8
5°	8035.0
7.5°	7818.4
10°	7526.9
12.5°	7144.0
15°	6702.7
17.5°	6228.1
20°	5762.0
22.5°	5295.5
25°	4804.4
27.5°	4238.2
30°	3588.6
32.5°	2830.9
35°	2081.6
37.5°	1465.4
40°	999.2
42.5°	624.4
45°	366.4
47.5°	208.2
50°	108.2
52.5°	50.0
55°	33.3
57.5°	24.9
60°	24.9
62.5°	16.8
65°	16.8
67.5°	8.4
70°	8.4
72.5°	8.4
75°	8.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)