

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685183

Luminaire Tested: **LX6C70D010 EX6709050 6LBNLI**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P685183
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C70D010 EX6709050 6LBNLI
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5901.0 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685183
CATALOG NUMBER: LX6C70D010 EX6709050 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685183

CATALOG NUMBER: LX6C70D010 EX6709050 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	736520
5°	688772
10°	561746
15°	413374
20°	284919
25°	211524
30°	158885
35°	99080
40°	48097
45°	16498
50°	2166
55°	1634
60°	943
65°	1116
70°	1378
75°	0
80°	0
85°	0



TEST NUMBER: P685183

CATALOG NUMBER: LX6C70D010 EX6709050 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1117.0	18.9
10°-20°	2005.0	34.0
20°-30°	1621.1	27.5
30°-40°	933.8	15.8
40°-50°	197.4	3.3
50°-60°	17.0	0.3
60°-70°	8.5	0.1
70°-80°	1.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4743.1	80.4
0°-40°	5676.9	96.2
0°-60°	5891.4	99.8
0°-90°	5901.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5901.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13435	
5°	12516	###
15°	7284	2005
25°	3497	1621
35°	1480	934
45°	213	197
55°	17	17
65°	9	9
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685183

CATALOG NUMBER: LX6C70D010 EX6709050 6LBNLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	13435.2
2.5°	13273.7
5°	12516.4
7.5°	11427.2
10°	10091.4
12.5°	8721.6
15°	7283.6
17.5°	5896.6
20°	4883.9
22.5°	4109.7
25°	3497.0
27.5°	2978.1
30°	2510.0
32.5°	1991.1
35°	1480.5
37.5°	1029.5
40°	672.1
42.5°	408.5
45°	212.8
47.5°	85.0
50°	25.4
52.5°	25.4
55°	17.1
57.5°	17.1
60°	8.6
62.5°	8.6
65°	8.6
67.5°	8.6
70°	8.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)