

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856668

Luminaire Tested: **LD6C75D010 EU6759027 6LBWLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P856668  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C75D010 EU6759027 6LBWLI  
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LBW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8184.0 lumens  
Efficiency: N/A  
Efficacy: 100.4 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 81.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856668

CATALOG NUMBER: LD6C75D010 EU6759027 6LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P856668

CATALOG NUMBER: LD6C75D010 EU6759027 6LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92																			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																			
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76																			
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69																			
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63																			
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57																			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																			
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44																			
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	280285
5°	282880
10°	290793
15°	298066
20°	302590
25°	296340
30°	277828
35°	248398
40°	201198
45°	133091
50°	67273
55°	28386
60°	9144
65°	3593
70°	2997
75°	1970
80°	0
85°	0



TEST NUMBER: P856668

CATALOG NUMBER: LD6C75D010 EU6759027 6LBWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	493.2	6.0
10°-20°	1482.5	18.1
20°-30°	2234.7	27.3
30°-40°	2287.4	27.9
40°-50°	1332.6	16.3
50°-60°	306.2	3.7
60°-70°	37.6	0.5
70°-80°	9.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4210.4	51.4
0°-40°	6497.8	79.4
0°-60°	8136.6	99.4
0°-90°	8184.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8184.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5113	
5°	5140	493
15°	5252	1482
25°	4899	2235
35°	3712	2287
45°	1717	1333
55°	297	306
65°	28	38
75°	9	10
85°	0	0
90°	0	



TEST NUMBER: P856668

CATALOG NUMBER: LD6C75D010 EU6759027 6LBWLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5112.8
2.5°	5103.4
5°	5140.5
7.5°	5177.5
10°	5223.9
12.5°	5233.2
15°	5251.9
17.5°	5233.2
20°	5186.8
22.5°	5038.3
25°	4899.2
27.5°	4676.7
30°	4389.0
32.5°	4092.1
35°	3711.7
37.5°	3284.6
40°	2811.5
42.5°	2282.6
45°	1716.7
47.5°	1196.9
50°	788.8
52.5°	501.2
55°	297.0
57.5°	157.8
60°	83.4
62.5°	46.4
65°	27.7
67.5°	27.7
70°	18.7
72.5°	9.3
75°	9.3
77.5°	9.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)