

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685187

Luminaire Tested: **LX6C75D010 EX6759027 6LBMLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P685187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EX6759027 6LBMLI
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7246.0 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685187
CATALOG NUMBER: LX6C75D010 EX6759027 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P685187

CATALOG NUMBER: LX6C75D010 EX6759027 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	497109
5°	492383
10°	466575
15°	423606
20°	374317
25°	323613
30°	252963
35°	155128
40°	79628
45°	31631
50°	10268
55°	3536
60°	3037
65°	2426
70°	1491
75°	1970
80°	0
85°	0



TEST NUMBER: P685187

CATALOG NUMBER: LX6C75D010 EX6759027 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	835.4	11.5
10°-20°	2079.8	28.7
20°-30°	2417.6	33.4
30°-40°	1480.5	20.4
40°-50°	367.6	5.1
50°-60°	42.9	0.6
60°-70°	16.1	0.2
70°-80°	6.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5332.7	73.6
0°-40°	6813.2	94.0
0°-60°	7223.8	99.7
0°-90°	7246.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7246.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9068	
5°	8948	835
15°	7464	2080
25°	5350	2418
35°	2318	1480
45°	408	368
55°	37	43
65°	19	16
75°	9	6
85°	0	0
90°	0	



TEST NUMBER: P685187

CATALOG NUMBER: LX6C75D010 EX6759027 6LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9068.0
2.5°	9058.7
5°	8947.6
7.5°	8706.4
10°	8381.7
12.5°	7955.4
15°	7463.9
17.5°	6935.5
20°	6416.3
22.5°	5896.9
25°	5350.1
27.5°	4719.5
30°	3996.2
32.5°	3152.5
35°	2318.0
37.5°	1631.8
40°	1112.7
42.5°	695.3
45°	408.0
47.5°	231.9
50°	120.4
52.5°	55.7
55°	37.0
57.5°	27.7
60°	27.7
62.5°	18.7
65°	18.7
67.5°	9.3
70°	9.3
72.5°	9.3
75°	9.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)