

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785485

Luminaire Tested: LERS6D02D010-EC6DR400210IC9030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P785485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D02D010-EC6DR400210IC9030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 695.2 lumens
Efficiency: N/A
Efficacy: 136.3 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785485

CATALOG NUMBER: LERS6D02D010-EC6DR400210IC9030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P785485

CATALOG NUMBER: LERS6D02D010-EC6DR400210IC9030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	97	96	95	93	92	91	89	88	87	84	82	81	77	74	72	69	68														
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96	95	93	92	91	89	88	87	84	82	81	77	74	72	69	68																				
	2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92	91	89	88	87	84	82	81	77	74	72	69	68																							
	3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88	87	84	82	81	77	74	72	69	68																										
	4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84	82	81	77	74	72	69	68																												
	5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81	77	74	72	69	68																														
	6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77	74	72	69	68																															
	7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74	72	69	68																																
	8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72	69	68																																	
	9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69	68																																		
	10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	69	68																																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176839
5°	175979
10°	166342
15°	141405
20°	96379
25°	40217
30°	12642
35°	5882
40°	3252
45°	1483
50°	731
55°	400
60°	197
65°	78
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1483 cd/sqm



TEST NUMBER: P785485

CATALOG NUMBER: LERS6D02D010-EC6DR400210IC9030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.8	21.6
10°-20°	335.6	48.3
20°-30°	168.0	24.2
30°-40°	30.8	4.4
40°-50°	8.5	1.2
50°-60°	2.0	0.3
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	653.5	94.0
0°-40°	684.3	98.4
0°-60°	694.8	99.9
0°-90°	695.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1618	
5°	1604	150
15°	1250	336
25°	334	168
35°	44	31
45°	10	8
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P785485

CATALOG NUMBER: LERS6D02D010-EC6DR400210IC9030-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1618.5
2.5°	1616.1
5°	1604.5
7.5°	1567.5
10°	1499.3
12.5°	1393.0
15°	1250.1
17.5°	1064.4
20°	828.9
22.5°	565.1
25°	333.6
27.5°	176.3
30°	100.2
32.5°	64.8
35°	44.1
37.5°	31.5
40°	22.8
42.5°	15.6
45°	9.6
47.5°	6.1
50°	4.3
52.5°	3.0
55°	2.1
57.5°	1.3
60°	0.9
62.5°	0.6
65°	0.3
67.5°	0.2
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)