

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684564

Luminaire Tested: **LX6C75D010 EX6C759027 6LBSH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EX6C759027 6LBSH
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8435.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684564

CATALOG NUMBER: LX6C75D010 EX6C759027 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684564

CATALOG NUMBER: LX6C75D010 EX6C759027 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	241839
5°	240710
10°	235745
15°	227169
20°	216721
25°	205046
30°	193410
35°	182111
40°	171478
45°	159846
50°	145744
55°	128712
60°	108950
65°	85547
70°	61036
75°	33445
80°	5872
85°	0



TEST NUMBER: P684564

CATALOG NUMBER: LX6C75D010 EX6C759027 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	413.2	4.9
10°-20°	1123.1	13.3
20°-30°	1559.7	18.5
30°-40°	1702.0	20.2
40°-50°	1587.8	18.8
50°-60°	1205.1	14.3
60°-70°	659.9	7.8
70°-80°	181.6	2.2
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3096.0	36.7
0°-40°	4798.1	56.9
0°-60°	7591.0	90.0
0°-90°	8435.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8435.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4412	
5°	4374	413
15°	4003	1123
25°	3390	1560
35°	2721	1702
45°	2062	1588
55°	1347	1205
65°	660	660
75°	158	182
85°	0	3
90°	0	



TEST NUMBER: P684564

CATALOG NUMBER: LX6C75D010 EX6C759027 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4411.5
2.5°	4411.5
5°	4374.2
7.5°	4318.5
10°	4235.0
12.5°	4123.5
15°	4002.7
17.5°	3854.2
20°	3714.9
22.5°	3547.7
25°	3389.9
27.5°	3232.0
30°	3055.4
32.5°	2888.2
35°	2721.2
37.5°	2554.0
40°	2396.2
42.5°	2229.0
45°	2061.8
47.5°	1894.6
50°	1708.9
52.5°	1532.4
55°	1346.7
57.5°	1170.2
60°	993.7
62.5°	817.4
65°	659.5
67.5°	510.7
70°	380.8
72.5°	260.0
75°	157.9
77.5°	74.4
80°	18.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)