

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684569

Luminaire Tested: **LX6C75D010 EX6C759030 6LBMH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684569  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C75D010 EX6C759030 6LBMH  
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBM TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6155.0 lumens  
Efficiency: N/A  
Efficacy: 75.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 81.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684569

CATALOG NUMBER: LX6C75D010 EX6C759030 6LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P684569

CATALOG NUMBER: LX6C75D010 EX6C759030 6LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	333926
5°	327949
10°	311194
15°	291818
20°	271769
25°	250412
30°	208646
35°	147057
40°	93718
45°	55890
50°	32988
55°	20989
60°	14451
65°	10261
70°	7069
75°	5592
80°	2747
85°	0



TEST NUMBER: P684569

CATALOG NUMBER: LX6C75D010 EX6C759030 6LBMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	556.9	9.0
10°-20°	1440.8	23.4
20°-30°	1866.9	30.3
30°-40°	1386.0	22.5
40°-50°	585.1	9.5
50°-60°	207.7	3.4
60°-70°	80.2	1.3
70°-80°	27.8	0.5
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3864.6	62.8
0°-40°	5250.6	85.3
0°-60°	6043.5	98.2
0°-90°	6155.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6155.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6091	
5°	5960	557
15°	5142	1441
25°	4140	1867
35°	2197	1386
45°	721	585
55°	220	208
65°	79	80
75°	26	28
85°	0	4
90°	0	



TEST NUMBER: P684569

CATALOG NUMBER: LX6C75D010 EX6C759030 6LBMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6091.3
2.5°	6073.6
5°	5959.5
7.5°	5792.3
10°	5590.4
12.5°	5370.4
15°	5141.8
17.5°	4887.1
20°	4658.5
22.5°	4421.2
25°	4139.9
27.5°	3753.0
30°	3296.1
32.5°	2759.8
35°	2197.4
37.5°	1722.8
40°	1309.6
42.5°	975.6
45°	720.9
47.5°	527.3
50°	386.8
52.5°	290.0
55°	219.6
57.5°	166.9
60°	131.8
62.5°	96.8
65°	79.1
67.5°	61.4
70°	44.1
72.5°	35.0
75°	26.4
77.5°	17.7
80°	8.7
82.5°	8.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)