

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P583010

Luminaire Tested: **LX6C75D010 EU6759035 6LBHYLI**

Issue Date: 8/31/2023



Test Information

Test Method: LM-79-08
Report Number: P583010
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)
Test Lab: INNOVATION CENTER
Issue Date: 8/31/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EU6759035 6LBHYLI
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LCHYP TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5630.0 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P583010

CATALOG NUMBER: LX6C75D010 EU6759035 6LBHYLI

Luminous Intensity Polar Plot





TEST NUMBER: P583010

CATALOG NUMBER: LX6C75D010 EU6759035 6LBHYLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																											
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																											
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																											
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																											
5	100	94	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82																											
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																											
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	76																											
8	91	83	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74																											
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	72	71																											
10	85	78	74	71	84	78	73	71	77	73	70	76	73	70	76	72	70	69																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	954759
5°	930655
10°	789025
15°	511410
20°	317594
25°	170937
30°	58750
35°	23664
40°	6326
45°	2822
50°	1109
55°	497
60°	285
65°	337
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P583010

CATALOG NUMBER: LX6C75D010 EU6759035 6LBHYLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1525.4	27.1
10°-20°	2515.8	44.7
20°-30°	1304.4	23.2
30°-40°	247.0	4.4
40°-50°	31.2	0.6
50°-60°	4.6	0.1
60°-70°	1.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5345.6	94.9
0°-40°	5592.6	99.3
0°-60°	5628.4	100.0
0°-90°	5630.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5630.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17416	
5°	16912	###
15°	9011	2516
25°	2826	1304
35°	354	247
45°	36	31
55°	5	5
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P583010

CATALOG NUMBER: LX6C75D010 EU6759035 6LBHYLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	17416.2
2.5°	17387.6
5°	16911.9
7.5°	15819.9
10°	14174.3
12.5°	11696.6
15°	9011.0
17.5°	6842.7
20°	5444.0
22.5°	4058.3
25°	2826.0
27.5°	1736.7
30°	928.1
32.5°	626.6
35°	353.6
37.5°	153.4
40°	88.4
42.5°	57.2
45°	36.4
47.5°	20.8
50°	13.0
52.5°	5.2
55°	5.2
57.5°	2.6
60°	2.6
62.5°	2.6
65°	2.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)