

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685198

Luminaire Tested: **LX6C75D010 EX6759035 6LBNLI**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P685198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EX6759035 6LBNLI
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6788.9 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685198

CATALOG NUMBER: LX6C75D010 EX6759035 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685198

CATALOG NUMBER: LX6C75D010 EX6759035 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95																											
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89																											
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85																											
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80																											
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76																											
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72																											
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68																											
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65																											
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62																											
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	847350
5°	792420
10°	646275
15°	475576
20°	327798
25°	243353
30°	182794
35°	113990
40°	55332
45°	18979
50°	2490
55°	1883
60°	1074
65°	1271
70°	1571
75°	0
80°	0
85°	0



TEST NUMBER: P685198

CATALOG NUMBER: LX6C75D010 EX6759035 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1285.1	18.9
10°-20°	2306.7	34.0
20°-30°	1865.0	27.5
30°-40°	1074.4	15.8
40°-50°	227.1	3.3
50°-60°	19.6	0.3
60°-70°	9.7	0.1
70°-80°	1.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5456.9	80.4
0°-40°	6531.2	96.2
0°-60°	6777.9	99.8
0°-90°	6788.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6788.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15457	
5°	14400	###
15°	8380	2307
25°	4023	1865
35°	1703	1074
45°	245	227
55°	20	20
65°	10	10
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685198

CATALOG NUMBER: LX6C75D010 EX6759035 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	15456.9
2.5°	15271.2
5°	14399.9
7.5°	13146.8
10°	11609.9
12.5°	10034.0
15°	8379.6
17.5°	6784.0
20°	5618.9
22.5°	4728.2
25°	4023.2
27.5°	3426.3
30°	2887.7
32.5°	2290.8
35°	1703.3
37.5°	1184.4
40°	773.2
42.5°	470.0
45°	244.8
47.5°	97.8
50°	29.2
52.5°	29.2
55°	19.7
57.5°	19.7
60°	9.8
62.5°	9.8
65°	9.8
67.5°	9.8
70°	9.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)