

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684578

Luminaire Tested: **LX6C75D010 EX6C759035 6LBSH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684578
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EX6C759035 6LBSH
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8893.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684578

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684578

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	254969
5°	253780
10°	248542
15°	239508
20°	228488
25°	216176
30°	203917
35°	192002
40°	180789
45°	168521
50°	153658
55°	135708
60°	114859
65°	90191
70°	64354
75°	35266
80°	6219
85°	0



TEST NUMBER: P684578

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	435.6	4.9
10°-20°	1184.1	13.3
20°-30°	1644.4	18.5
30°-40°	1794.5	20.2
40°-50°	1674.0	18.8
50°-60°	1270.6	14.3
60°-70°	695.7	7.8
70°-80°	191.5	2.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3264.1	36.7
0°-40°	5058.6	56.9
0°-60°	8003.2	90.0
0°-90°	8893.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8893.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4651	
5°	4612	436
15°	4220	1184
25°	3574	1644
35°	2869	1794
45°	2174	1674
55°	1420	1271
65°	695	696
75°	166	191
85°	0	3
90°	0	



TEST NUMBER: P684578

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4651.0
2.5°	4651.0
5°	4611.7
7.5°	4553.0
10°	4464.9
12.5°	4347.4
15°	4220.1
17.5°	4063.4
20°	3916.6
22.5°	3740.4
25°	3573.9
27.5°	3407.5
30°	3221.4
32.5°	3045.1
35°	2869.0
37.5°	2692.7
40°	2526.3
42.5°	2350.0
45°	2173.7
47.5°	1997.4
50°	1801.7
52.5°	1615.6
55°	1419.9
57.5°	1233.8
60°	1047.6
62.5°	861.7
65°	695.3
67.5°	538.5
70°	401.5
72.5°	274.1
75°	166.5
77.5°	78.4
80°	19.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)