

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684579

Luminaire Tested: **LX6C75D010 EX6C759035 6LBWH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EX6C759035 6LBWH
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7554.0 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684579

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P684579

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	255407
5°	255321
10°	253358
15°	251659
20°	247827
25°	242161
30°	228010
35°	206351
40°	172309
45°	132029
50°	93507
55°	58951
60°	33254
65°	21585
70°	14105
75°	10357
80°	6219
85°	6227



TEST NUMBER: P684579

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	440.1	5.8
10°-20°	1248.7	16.5
20°-30°	1830.8	24.2
30°-40°	1905.4	25.2
40°-50°	1318.3	17.5
50°-60°	574.0	7.6
60°-70°	176.0	2.3
70°-80°	52.8	0.7
80°-90°	8.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3519.5	46.6
0°-40°	5424.9	71.8
0°-60°	7317.2	96.9
0°-90°	7554.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7554.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4659	
5°	4640	440
15°	4434	1249
25°	4004	1831
35°	3083	1905
45°	1703	1318
55°	617	574
65°	166	176
75°	49	53
85°	10	8
90°	0	



TEST NUMBER: P684579

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4659.0
2.5°	4668.9
5°	4639.7
7.5°	4600.6
10°	4551.4
12.5°	4502.5
15°	4434.2
17.5°	4345.9
20°	4248.1
22.5°	4140.4
25°	4003.5
27.5°	3827.2
30°	3602.0
32.5°	3367.0
35°	3083.4
37.5°	2770.2
40°	2407.8
42.5°	2045.7
45°	1703.0
47.5°	1380.0
50°	1096.4
52.5°	832.2
55°	616.8
57.5°	440.5
60°	303.3
62.5°	225.2
65°	166.4
67.5°	127.4
70°	88.0
72.5°	68.6
75°	48.9
77.5°	29.2
80°	19.7
82.5°	9.9
85°	9.9
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)