

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P583012

Luminaire Tested: **LX6C75D010 EU6759050 6LBHYLI**

Issue Date: 8/31/2023



Test Information

Test Method: LM-79-08
Report Number: P583012
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)
Test Lab: INNOVATION CENTER
Issue Date: 8/31/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EU6759050 6LBHYLI
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LCHYP TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5754.1 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P583012

CATALOG NUMBER: LX6C75D010 EU6759050 6LBHYLI

Luminous Intensity Polar Plot





TEST NUMBER: P583012

CATALOG NUMBER: LX6C75D010 EU6759050 6LBHYLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99 | 99 | 98 | 96 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98 | 99 | 97 | 96 | 97 | 95 | 94 | 92 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 98 | 95 | 93 | 96 | 93 | 91 | 94 | 92 | 90 | 89 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | 103 | 98 | 93 | 90 | 102 | 96 | 93 | 90 | 94 | 91 | 89 | 93 | 90 | 88 | 91 | 89 | 87 | 85 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5 | 100 | 94 | 89 | 86 | 98 | 93 | 89 | 86 | 91 | 87 | 85 | 89 | 86 | 84 | 88 | 85 | 83 | 82 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6 | 97 | 90 | 85 | 82 | 95 | 89 | 85 | 82 | 88 | 84 | 81 | 87 | 83 | 81 | 85 | 83 | 80 | 79 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7 | 93 | 87 | 82 | 79 | 92 | 86 | 82 | 79 | 85 | 81 | 78 | 84 | 80 | 78 | 83 | 80 | 78 | 76 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8 | 91 | 83 | 79 | 76 | 90 | 83 | 79 | 76 | 82 | 78 | 75 | 81 | 78 | 75 | 80 | 77 | 75 | 74 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9 | 88 | 81 | 76 | 73 | 87 | 80 | 76 | 73 | 79 | 76 | 73 | 79 | 75 | 73 | 78 | 75 | 72 | 71 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10 | 85 | 78 | 74 | 71 | 84 | 78 | 73 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 76 | 72 | 70 | 69 | | | | | | | | | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 975788 |
| 5° | 951153 |
| 10° | 806398 |
| 15° | 522676 |
| 20° | 324589 |
| 25° | 174706 |
| 30° | 60047 |
| 35° | 24186 |
| 40° | 6462 |
| 45° | 2884 |
| 50° | 1134 |
| 55° | 507 |
| 60° | 296 |
| 65° | 350 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P583012

CATALOG NUMBER: LX6C75D010 EU6759050 6LBHYLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1559.0 | 27.1 |
| 10°-20° | 2571.3 | 44.7 |
| 20°-30° | 1333.1 | 23.2 |
| 30°-40° | 252.5 | 4.4 |
| 40°-50° | 31.9 | 0.6 |
| 50°-60° | 4.7 | 0.1 |
| 60°-70° | 1.7 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 5463.4 | 94.9 |
| 0°-40° | 5715.8 | 99.3 |
| 0°-60° | 5752.4 | 100.0 |
| 0°-90° | 5754.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5754.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 17800 | |
| 5° | 17284 | ### |
| 15° | 9210 | 2571 |
| 25° | 2888 | 1333 |
| 35° | 361 | 252 |
| 45° | 37 | 32 |
| 55° | 5 | 5 |
| 65° | 3 | 2 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P583012

CATALOG NUMBER: LX6C75D010 EU6759050 6LBHYLI

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|---------|
| 0° | 17799.8 |
| 2.5° | 17770.6 |
| 5° | 17284.4 |
| 7.5° | 16168.4 |
| 10° | 14486.4 |
| 12.5° | 11954.2 |
| 15° | 9209.5 |
| 17.5° | 6993.5 |
| 20° | 5563.9 |
| 22.5° | 4147.7 |
| 25° | 2888.3 |
| 27.5° | 1774.9 |
| 30° | 948.6 |
| 32.5° | 640.4 |
| 35° | 361.4 |
| 37.5° | 156.8 |
| 40° | 90.3 |
| 42.5° | 58.5 |
| 45° | 37.2 |
| 47.5° | 21.3 |
| 50° | 13.3 |
| 52.5° | 5.3 |
| 55° | 5.3 |
| 57.5° | 2.7 |
| 60° | 2.7 |
| 62.5° | 2.7 |
| 65° | 2.7 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)