

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685208

Luminaire Tested: **LX6C75D010 EX6759050 6LBNLI**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P685208  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C75D010 EX6759050 6LBNLI  
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LBN TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6939.0 lumens  
Efficiency: N/A  
Efficacy: 85.1 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 81.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685208

CATALOG NUMBER: LX6C75D010 EX6759050 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685208

CATALOG NUMBER: LX6C75D010 EX6759050 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	866076
5°	809925
10°	660559
15°	486087
20°	335037
25°	248730
30°	186833
35°	116506
40°	56556
45°	19397
50°	2541
55°	1921
60°	1107
65°	1310
70°	1619
75°	0
80°	0
85°	0



TEST NUMBER: P685208

CATALOG NUMBER: LX6C75D010 EX6759050 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1313.5	18.9
10°-20°	2357.7	34.0
20°-30°	1906.2	27.5
30°-40°	1098.1	15.8
40°-50°	232.1	3.3
50°-60°	20.0	0.3
60°-70°	10.0	0.1
70°-80°	1.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5577.4	80.4
0°-40°	6675.5	96.2
0°-60°	6927.7	99.8
0°-90°	6939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6939.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15798	
5°	14718	###
15°	8565	2358
25°	4112	1906
35°	1741	1098
45°	250	232
55°	20	20
65°	10	10
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685208

CATALOG NUMBER: LX6C75D010 EX6759050 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	15798.5
2.5°	15608.6
5°	14718.0
7.5°	13437.3
10°	11866.5
12.5°	10255.7
15°	8564.8
17.5°	6933.8
20°	5743.0
22.5°	4832.7
25°	4112.1
27.5°	3502.0
30°	2951.5
32.5°	2341.4
35°	1740.9
37.5°	1210.6
40°	790.3
42.5°	480.4
45°	250.2
47.5°	100.0
50°	29.8
52.5°	29.8
55°	20.1
57.5°	20.1
60°	10.1
62.5°	10.1
65°	10.1
67.5°	10.1
70°	10.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)