

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785715

Luminaire Tested: LERS6D05D010-EC6DR200210IC9050-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P785715
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D05D010-EC6DR200210IC9050-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 750.7 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785715

CATALOG NUMBER: LERS6D05D010-EC6DR200210IC9050-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P785715

CATALOG NUMBER: LERS6D05D010-EC6DR200210IC9050-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	100	99	98	98	96	95	94													
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	98	96	95	98	96	95	94													
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	98	96	95	98	96	95	94													
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	93	91	89	93	91	89	88													
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	91	88	86	91	88	86	85													
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	88	86	84	88	86	84	83													
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	86	84	82	86	84	82	81													
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80	84	82	80	79													
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	82	80	78	82	80	78	77													
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	81	78	76	81	78	76	75													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	466860
5°	421197
10°	236404
15°	120162
20°	50881
25°	23484
30°	12427
35°	6696
40°	3580
45°	2117
50°	1224
55°	648
60°	415
65°	284
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2117 cd/sqm



TEST NUMBER: P785715

CATALOG NUMBER: LERS6D05D010-EC6DR200210IC9050-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.2	40.5
10°-20°	299.6	39.9
20°-30°	97.9	13.0
30°-40°	33.3	4.4
40°-50°	11.2	1.5
50°-60°	3.4	0.5
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.7	93.5
0°-40°	735.0	97.9
0°-60°	749.6	99.8
0°-90°	750.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	750.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4273	
5°	3840	304
15°	1062	300
25°	195	98
35°	50	33
45°	14	11
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P785715

CATALOG NUMBER: LERS6D05D010-EC6DR200210IC9050-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4272.9
0.5°	4272.9
1°	4267.6
1.5°	4256.9
2°	4237.5
2.5°	4211.7
3°	4175.1
3.5°	4124.2
4°	4048.4
4.5°	3956.4
5°	3840.3
5.5°	3687.7
6°	3531.4
6.5°	3352.1
7°	3176.7
7.5°	2971.3
8°	2787.9
8.5°	2603.3
9°	2432.9
9.5°	2276.5
10°	2130.8
12.5°	1530.0
15°	1062.3
17.5°	694.0
20°	437.6
22.5°	283.5
25°	194.8
27.5°	137.0
30°	98.5
32.5°	70.8
35°	50.2
37.5°	35.0
40°	25.1
42.5°	18.3
45°	13.7
47.5°	10.7
50°	7.2
52.5°	4.6
55°	3.4
57.5°	2.7
60°	1.9
62.5°	1.5
65°	1.1



TEST NUMBER: P785715

CATALOG NUMBER: LERS6D05D010-EC6DR200210IC9050-6LBS1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.8
70°		0.4

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)