

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P799240

Luminaire Tested: **LD6C08D010 EU6089027 6LBMDSWLI**

Issue Date: 4/12/2024

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P799240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2309-186-5)
Test Lab: INNOVATION CENTER
Issue Date: 4/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C08D010 EU6089027 6LBMDSWLI
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND 6LBMDSW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 714.0 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P799240

CATALOG NUMBER: LD6C08D010 EU6089027 6LBMDSWLI

Luminous Intensity Polar Plot





TEST NUMBER: P799240

CATALOG NUMBER: LD6C08D010 EU6089027 6LBMDSWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|--|--|--|---|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 | | | | |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98 | 97 | 97 | 95 | 94 | 92 | | | | 92 | | | | |
| 2 | 107 | 102 | 97 | 94 | 105 | 100 | 96 | 93 | 97 | 93 | 91 | 94 | 91 | 89 | 91 | 89 | 87 | 85 | | | | 85 | | | | |
| 3 | 101 | 94 | 89 | 85 | 99 | 93 | 88 | 84 | 90 | 86 | 83 | 88 | 84 | 81 | 85 | 83 | 80 | 78 | | | | 78 | | | | |
| 4 | 96 | 88 | 82 | 77 | 94 | 87 | 81 | 77 | 84 | 80 | 76 | 82 | 78 | 75 | 80 | 77 | 74 | 73 | | | | 73 | | | | |
| 5 | 91 | 82 | 76 | 71 | 89 | 81 | 75 | 71 | 79 | 74 | 70 | 77 | 73 | 70 | 76 | 72 | 69 | 67 | | | | 67 | | | | |
| 6 | 86 | 77 | 70 | 66 | 84 | 76 | 70 | 66 | 74 | 69 | 65 | 73 | 68 | 65 | 71 | 67 | 64 | 63 | | | | 63 | | | | |
| 7 | 82 | 72 | 66 | 61 | 80 | 71 | 65 | 61 | 70 | 65 | 61 | 69 | 64 | 60 | 68 | 63 | 60 | 59 | | | | 59 | | | | |
| 8 | 78 | 68 | 61 | 57 | 76 | 67 | 61 | 57 | 66 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 56 | 55 | | | | 55 | | | | |
| 9 | 74 | 64 | 58 | 54 | 73 | 63 | 57 | 54 | 62 | 57 | 53 | 61 | 57 | 53 | 61 | 56 | 53 | 52 | | | | 52 | | | | |
| 10 | 70 | 60 | 54 | 50 | 69 | 60 | 54 | 50 | 59 | 54 | 50 | 58 | 53 | 50 | 58 | 53 | 50 | 49 | | | | 49 | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 90° | 180° |
|-----|-------|-------|-------|
| 0° | 45462 | 45462 | 45462 |
| 5° | 47193 | 44398 | 43391 |
| 10° | 45986 | 41644 | 39812 |
| 15° | 43127 | 38054 | 36408 |
| 20° | 37862 | 33877 | 33230 |
| 25° | 30619 | 27830 | 28973 |
| 30° | 21288 | 19383 | 23193 |
| 35° | 13124 | 11879 | 17500 |
| 40° | 7428 | 6655 | 11622 |
| 45° | 3605 | 3442 | 7931 |
| 50° | 1373 | 1373 | 6746 |
| 55° | 755 | 889 | 6222 |
| 60° | 548 | 702 | 5098 |
| 65° | 467 | 610 | 4177 |
| 70° | 401 | 513 | 3446 |
| 75° | 381 | 530 | 2965 |
| 80° | 221 | 442 | 2147 |
| 85° | 252 | 881 | 2013 |



TEST NUMBER: P799240

CATALOG NUMBER: LD6C08D010 EU6089027 6LBMDSWLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 75.9 | 10.6 |
| 10°-20° | 190.8 | 26.7 |
| 20°-30° | 214.8 | 30.1 |
| 30°-40° | 133.0 | 18.6 |
| 40°-50° | 53.0 | 7.4 |
| 50°-60° | 24.1 | 3.4 |
| 60°-70° | 13.9 | 1.9 |
| 70°-80° | 6.6 | 0.9 |
| 80°-90° | 1.9 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 481.5 | 67.4 |
| 0°-40° | 614.6 | 86.1 |
| 0°-60° | 691.7 | 96.9 |
| 0°-90° | 714.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 714.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 45° | 90° | 135° | 180° | Flux |
|-----|-----|-----|-----|------|------|------|
| 0° | 829 | 829 | 829 | 829 | 829 | |
| 5° | 858 | 842 | 807 | 789 | 788 | 81 |
| 15° | 760 | 727 | 670 | 643 | 642 | 210 |
| 25° | 506 | 493 | 460 | 472 | 479 | 228 |
| 35° | 196 | 195 | 178 | 247 | 262 | 126 |
| 45° | 46 | 46 | 44 | 97 | 102 | 39 |
| 55° | 8 | 8 | 9 | 57 | 65 | 8 |
| 65° | 4 | 3 | 5 | 32 | 32 | 3 |
| 75° | 2 | 2 | 2 | 14 | 14 | 2 |
| 85° | 0 | 0 | 1 | 3 | 3 | 0 |
| 90° | 0 | 0 | 0 | 0 | 0 | |



TEST NUMBER: P799240

CATALOG NUMBER: LD6C08D010 EU6089027 6LBMDSWLI

CANDELA DISTRIBUTION (FULL):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° |
|-------|-------|-------|-------|-------|-------|--------|-------|--------|-------|
| 0° | 829.3 | 829.3 | 829.3 | 829.3 | 829.3 | 829.3 | 829.3 | 829.3 | 829.3 |
| 2.5° | 848.3 | 840.4 | 838.6 | 831.8 | 820.4 | 813.9 | 810.0 | 807.1 | 812.1 |
| 5° | 857.6 | 849.0 | 841.8 | 827.9 | 806.8 | 795.0 | 789.2 | 784.6 | 788.5 |
| 7.5° | 850.8 | 838.6 | 828.9 | 809.6 | 782.8 | 764.5 | 756.7 | 751.3 | 754.9 |
| 10° | 826.1 | 811.4 | 800.3 | 777.4 | 748.1 | 726.3 | 716.6 | 711.6 | 715.2 |
| 12.5° | 793.9 | 781.7 | 764.9 | 739.9 | 708.4 | 685.5 | 678.3 | 674.4 | 675.8 |
| 15° | 759.9 | 745.6 | 727.0 | 701.9 | 670.5 | 647.6 | 643.3 | 640.8 | 641.5 |
| 17.5° | 710.5 | 696.6 | 680.5 | 656.1 | 627.2 | 608.6 | 608.6 | 606.8 | 607.8 |
| 20° | 649.0 | 641.5 | 625.7 | 605.3 | 580.7 | 563.8 | 569.2 | 567.4 | 569.6 |
| 22.5° | 582.4 | 576.7 | 563.1 | 546.3 | 525.6 | 512.3 | 524.1 | 523.8 | 526.6 |
| 25° | 506.2 | 501.9 | 492.6 | 478.3 | 460.1 | 451.9 | 471.5 | 471.5 | 479.0 |
| 27.5° | 422.2 | 417.9 | 411.4 | 399.3 | 384.2 | 381.7 | 410.7 | 414.3 | 422.5 |
| 30° | 336.3 | 333.4 | 329.9 | 318.8 | 306.2 | 310.9 | 351.0 | 357.1 | 366.4 |
| 32.5° | 259.7 | 257.9 | 256.9 | 246.9 | 235.8 | 251.2 | 296.9 | 304.8 | 314.1 |
| 35° | 196.1 | 192.1 | 195.0 | 187.5 | 177.5 | 196.8 | 247.2 | 254.0 | 261.5 |
| 37.5° | 144.5 | 141.7 | 144.2 | 138.8 | 129.9 | 151.0 | 198.6 | 202.9 | 207.9 |
| 40° | 103.8 | 101.2 | 103.4 | 100.2 | 93.0 | 112.7 | 155.6 | 160.3 | 162.4 |
| 42.5° | 73.7 | 69.4 | 71.6 | 69.0 | 65.5 | 84.8 | 122.4 | 126.6 | 127.4 |
| 45° | 46.5 | 45.1 | 46.5 | 45.1 | 44.4 | 63.0 | 96.6 | 100.5 | 102.3 |
| 47.5° | 28.3 | 26.5 | 26.5 | 25.8 | 26.5 | 46.5 | 79.8 | 85.5 | 88.4 |
| 50° | 16.1 | 15.4 | 15.0 | 14.7 | 16.1 | 36.5 | 69.0 | 75.5 | 79.1 |
| 52.5° | 10.7 | 10.4 | 10.4 | 10.0 | 11.8 | 30.8 | 62.3 | 68.0 | 71.6 |
| 55° | 7.9 | 7.5 | 7.5 | 7.5 | 9.3 | 26.5 | 57.2 | 61.9 | 65.1 |
| 57.5° | 6.1 | 6.1 | 6.1 | 5.7 | 7.9 | 22.5 | 51.2 | 53.7 | 56.2 |
| 60° | 5.0 | 4.7 | 4.7 | 4.7 | 6.4 | 19.3 | 44.0 | 45.1 | 46.5 |
| 62.5° | 3.9 | 3.9 | 3.9 | 3.9 | 5.4 | 17.2 | 37.9 | 37.9 | 38.6 |
| 65° | 3.6 | 3.2 | 3.2 | 3.2 | 4.7 | 15.0 | 31.8 | 31.5 | 32.2 |
| 67.5° | 2.9 | 2.9 | 2.9 | 2.9 | 3.9 | 12.9 | 26.1 | 25.8 | 26.5 |
| 70° | 2.5 | 2.5 | 2.5 | 2.5 | 3.2 | 10.7 | 21.1 | 20.8 | 21.5 |
| 72.5° | 2.1 | 2.1 | 2.1 | 2.1 | 2.9 | 8.9 | 16.8 | 16.8 | 17.2 |
| 75° | 1.8 | 1.8 | 1.8 | 1.8 | 2.5 | 6.8 | 13.6 | 13.6 | 14.0 |
| 77.5° | 1.4 | 1.4 | 1.4 | 1.4 | 1.8 | 5.4 | 10.4 | 10.0 | 10.0 |
| 80° | 0.7 | 1.1 | 1.1 | 1.1 | 1.4 | 3.9 | 7.5 | 6.8 | 6.8 |
| 82.5° | 0.4 | 0.7 | 0.7 | 0.7 | 1.4 | 2.9 | 5.0 | 4.7 | 4.7 |
| 85° | 0.4 | 0.4 | 0.4 | 1.1 | 1.4 | 2.1 | 3.2 | 3.2 | 3.2 |
| 87.5° | 0.0 | 0.4 | 0.7 | 1.4 | 1.8 | 1.8 | 2.1 | 1.8 | 1.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)