

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685221

Luminaire Tested: **LX6C08D010 EX6089030 6LRMDLI**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P685221
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C08D010 EX6089030 6LRMDLI
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 674.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685221

CATALOG NUMBER: LX6C08D010 EX6089030 6LRMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P685221

CATALOG NUMBER: LX6C08D010 EX6089030 6LRMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89		
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83		
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78		
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74		
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70		
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66		
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62		
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59		
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55187
5°	55294
10°	52693
15°	45375
20°	37377
25°	29197
30°	21086
35°	10795
40°	5267
45°	2186
50°	401
55°	229
60°	153
65°	117
70°	80
75°	64
80°	63
85°	0



TEST NUMBER: P685221

CATALOG NUMBER: LX6C08D010 EX6089030 6LRMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	14.0
10°-20°	221.6	32.9
20°-30°	219.5	32.6
30°-40°	111.2	16.5
40°-50°	24.0	3.6
50°-60°	2.3	0.3
60°-70°	0.9	0.1
70°-80°	0.3	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.2	79.4
0°-40°	646.5	95.9
0°-60°	672.7	99.8
0°-90°	674.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	674.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1007	
5°	1005	94
15°	800	222
25°	483	219
35°	161	111
45°	28	24
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P685221

CATALOG NUMBER: LX6C08D010 EX6089030 6LRMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1006.7
2.5°	1007.9
5°	1004.8
7.5°	989.0
10°	946.6
12.5°	878.4
15°	799.5
17.5°	718.6
20°	640.7
22.5°	562.8
25°	482.7
27.5°	400.9
30°	333.1
32.5°	256.6
35°	161.3
37.5°	108.5
40°	73.6
42.5°	47.6
45°	28.2
47.5°	12.6
50°	4.7
52.5°	3.1
55°	2.4
57.5°	1.7
60°	1.4
62.5°	1.0
65°	0.9
67.5°	0.7
70°	0.5
72.5°	0.3
75°	0.3
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)