

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685222

Luminaire Tested: **LX6C08D010 EX6089035 6LBMLI**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P685222  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C08D010 EX6089035 6LBMLI  
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 6LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 815.1 lumens  
Efficiency: N/A  
Efficacy: 82.3 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685222

CATALOG NUMBER: LX6C08D010 EX6089035 6LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685222

CATALOG NUMBER: LX6C08D010 EX6089035 6LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	55911
5°	55382
10°	52476
15°	47645
20°	42103
25°	36401
30°	28454
35°	17447
40°	8952
45°	3559
50°	1151
55°	401
60°	340
65°	272
70°	176
75°	233
80°	0
85°	0



TEST NUMBER: P685222

CATALOG NUMBER: LX6C08D010 EX6089035 6LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.0	11.5
10°-20°	233.9	28.7
20°-30°	271.9	33.4
30°-40°	166.5	20.4
40°-50°	41.3	5.1
50°-60°	4.8	0.6
60°-70°	1.8	0.2
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.8	73.6
0°-40°	766.3	94.0
0°-60°	812.5	99.7
0°-90°	815.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	815.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1020	
5°	1006	94
15°	840	234
25°	602	272
35°	261	167
45°	46	41
55°	4	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P685222

CATALOG NUMBER: LX6C08D010 EX6089035 6LBMLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1019.9
2.5°	1018.9
5°	1006.4
7.5°	979.3
10°	942.7
12.5°	894.8
15°	839.5
17.5°	780.1
20°	721.7
22.5°	663.3
25°	601.8
27.5°	530.8
30°	449.5
32.5°	354.6
35°	260.7
37.5°	183.5
40°	125.1
42.5°	78.2
45°	45.9
47.5°	26.1
50°	13.5
52.5°	6.3
55°	4.2
57.5°	3.1
60°	3.1
62.5°	2.1
65°	2.1
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)