

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684616

Luminaire Tested: **LX6C08D010 EX6C089035 6LBNH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P684616  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C08D010 EX6C089035 6LBNH  
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 6LBN TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 573.0 lumens  
Efficiency: N/A  
Efficacy: 57.9 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684616

CATALOG NUMBER: LX6C08D010 EX6C089035 6LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P684616

CATALOG NUMBER: LX6C08D010 EX6C089035 6LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	40265
5°	39269
10°	36233
15°	32083
20°	27857
25°	23826
30°	19642
35°	12936
40°	6956
45°	3078
50°	1245
55°	898
60°	570
65°	415
70°	337
75°	233
80°	347
85°	0



TEST NUMBER: P684616

CATALOG NUMBER: LX6C08D010 EX6C089035 6LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	66.1	11.5
10°-20°	157.5	27.5
20°-30°	180.5	31.5
30°-40°	121.2	21.2
40°-50°	34.6	6.0
50°-60°	8.5	1.5
60°-70°	3.2	0.6
70°-80°	1.3	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	404.0	70.5
0°-40°	525.3	91.7
0°-60°	568.3	99.2
0°-90°	573.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	573.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	734	
5°	714	66
15°	565	158
25°	394	180
35°	193	121
45°	40	35
55°	9	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P684616

CATALOG NUMBER: LX6C08D010 EX6C089035 6LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	734.5
2.5°	729.3
5°	713.6
7.5°	685.4
10°	650.9
12.5°	607.0
15°	565.3
17.5°	521.4
20°	477.5
22.5°	435.7
25°	393.9
27.5°	355.2
30°	310.3
32.5°	250.7
35°	193.3
37.5°	141.0
40°	97.2
42.5°	63.7
45°	39.7
47.5°	24.0
50°	14.6
52.5°	11.5
55°	9.4
57.5°	7.3
60°	5.2
62.5°	4.2
65°	3.2
67.5°	2.1
70°	2.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)