

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785783

Luminaire Tested: LERS6D05D010-EC6DR350210IC9040-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P785783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D05D010-EC6DR350210IC9040-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1195.9 lumens
Efficiency: N/A
Efficacy: 159.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785783

CATALOG NUMBER: LERS6D05D010-EC6DR350210IC9040-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P785783

CATALOG NUMBER: LERS6D05D010-EC6DR350210IC9040-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96					96			
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92					92			
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88					88			
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84					84			
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81					81			
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78					78			
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75					75			
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72					72			
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70					70			
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68					68			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	359523
5°	351069
10°	316408
15°	245584
20°	139295
25°	54190
30°	20211
35°	11084
40°	7246
45°	4404
50°	2805
55°	1981
60°	1442
65°	801
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4404 cd/sqm



TEST NUMBER: P785783

CATALOG NUMBER: LERS6D05D010-EC6DR350210IC9040-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.4	24.6
10°-20°	574.8	48.1
20°-30°	234.4	19.6
30°-40°	56.1	4.7
40°-50°	23.4	2.0
50°-60°	9.7	0.8
60°-70°	3.0	0.3
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1103.6	92.3
0°-40°	1159.7	97.0
0°-60°	1192.7	99.7
0°-90°	1195.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1195.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3290	
5°	3201	294
15°	2171	575
25°	450	234
35°	83	56
45°	28	23
55°	10	10
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P785783

CATALOG NUMBER: LERS6D05D010-EC6DR350210IC9040-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3290.5
2.5°	3270.7
5°	3200.9
7.5°	3061.7
10°	2851.9
12.5°	2556.5
15°	2171.1
17.5°	1699.7
20°	1198.0
22.5°	763.9
25°	449.5
27.5°	254.1
30°	160.2
32.5°	112.5
35°	83.1
37.5°	64.2
40°	50.8
42.5°	39.1
45°	28.5
47.5°	21.4
50°	16.5
52.5°	13.1
55°	10.4
57.5°	8.4
60°	6.6
62.5°	4.8
65°	3.1
67.5°	1.1
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)