

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563985

Luminaire Tested: **LX6C08D010 EX6C089030 6LBNH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P563985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C08D010 EX6C089030 6LBNH
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LBN TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 574.7 lumens
Efficiency: N/A
Efficacy: 58.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563985

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P563985

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40392
5°	39390
10°	36344
15°	32180
20°	27938
25°	23899
30°	19706
35°	12976
40°	6970
45°	3093
50°	1245
55°	908
60°	570
65°	415
70°	337
75°	212
80°	316
85°	0



TEST NUMBER: P563985

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.3	11.5
10°-20°	158.0	27.5
20°-30°	181.0	31.5
30°-40°	121.6	21.2
40°-50°	34.7	6.0
50°-60°	8.5	1.5
60°-70°	3.2	0.6
70°-80°	1.2	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.2	70.5
0°-40°	526.9	91.7
0°-60°	570.1	99.2
0°-90°	574.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	574.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	737	
5°	716	66
15°	567	158
25°	395	181
35°	194	122
45°	40	35
55°	10	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P563985

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	736.8
2.5°	731.5
5°	715.8
7.5°	687.4
10°	652.9
12.5°	608.9
15°	567.0
17.5°	522.9
20°	478.9
22.5°	437.0
25°	395.1
27.5°	356.3
30°	311.3
32.5°	251.5
35°	193.9
37.5°	141.5
40°	97.4
42.5°	63.9
45°	39.9
47.5°	24.1
50°	14.6
52.5°	11.5
55°	9.5
57.5°	7.3
60°	5.2
62.5°	4.2
65°	3.2
67.5°	2.1
70°	2.1
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)