

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563987

Luminaire Tested: **LX6C08D010 EX6C089030 6LBWH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P563987  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C08D010 EX6C089030 6LBWH  
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LBW TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 808.6 lumens  
Efficiency: N/A  
Efficacy: 81.7 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563987

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P563987

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27339
5°	27333
10°	27120
15°	26941
20°	26532
25°	25919
30°	24409
35°	22091
40°	18449
45°	14133
50°	10012
55°	6308
60°	3552
65°	2309
70°	1523
75°	1101
80°	663
85°	629



TEST NUMBER: P563987

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.1	5.8
10°-20°	133.7	16.5
20°-30°	196.0	24.2
30°-40°	204.0	25.2
40°-50°	141.1	17.5
50°-60°	61.4	7.6
60°-70°	18.8	2.3
70°-80°	5.7	0.7
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	376.8	46.6
0°-40°	580.7	71.8
0°-60°	783.3	96.9
0°-90°	808.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	808.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	499	
5°	497	47
15°	475	134
25°	428	196
35°	330	204
45°	182	141
55°	66	61
65°	18	19
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P563987

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	498.7
2.5°	499.9
5°	496.7
7.5°	492.5
10°	487.2
12.5°	481.9
15°	474.7
17.5°	465.3
20°	454.8
22.5°	443.2
25°	428.5
27.5°	409.7
30°	385.6
32.5°	360.4
35°	330.1
37.5°	296.5
40°	257.8
42.5°	219.0
45°	182.3
47.5°	147.7
50°	117.4
52.5°	89.1
55°	66.0
57.5°	47.2
60°	32.4
62.5°	24.1
65°	17.8
67.5°	13.6
70°	9.5
72.5°	7.3
75°	5.2
77.5°	3.2
80°	2.1
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)