

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684652

Luminaire Tested: **LX6C80D010 EX6C809035 6LBLWWH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684652  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2107-320-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C80D010 EX6C809035 6LBLWWH  
Description: 6 INCH 8000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 6LRLWW TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7610.0 lumens  
Efficiency: N/A  
Efficacy: 85.0 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.08 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 89.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684652

CATALOG NUMBER: LX6C80D010 EX6C809035 6LBLWWH

### Luminous Intensity Polar Plot





TEST NUMBER: P684652

CATALOG NUMBER: LX6C80D010 EX6C809035 6LBLWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	81	85	82	80	78																			
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68																			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60																			
5	82	71	63	58	80	70	63	57	68	62	57	66	61	56	64	60	56	54																			
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48																			
7	71	59	52	46	70	59	51	46	57	51	46	56	50	45	55	49	45	43																			
8	67	55	47	42	65	54	47	42	53	46	42	52	46	41	51	45	41	39																			
9	63	51	43	38	62	50	43	38	49	42	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	38	35	33																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	229351	229351	229351
5°	230150	228059	225814
10°	229444	224356	221066
15°	228582	219723	214615
20°	228074	212486	206821
25°	222521	201090	196663
30°	211419	187295	184180
35°	191895	170533	169402
40°	168365	153473	152665
45°	144348	134099	135192
50°	124252	114299	113702
55°	108603	96503	90587
60°	95442	79095	61826
65°	83550	61291	37215
70°	71230	41241	21863
75°	57485	21456	11925
80°	39967	8429	6661
85°	15913	2642	3522



TEST NUMBER: P684652

CATALOG NUMBER: LX6C80D010 EX6C809035 6LBLWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	392.0	5.2
10°-20°	1094.7	14.4
20°-30°	1557.7	20.5
30°-40°	1639.6	21.5
40°-50°	1366.4	18.0
50°-60°	923.1	12.1
60°-70°	468.0	6.2
70°-80°	151.1	2.0
80°-90°	17.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3044.4	40.0
0°-40°	4684.0	61.6
0°-60°	6973.5	91.6
0°-90°	7610.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7610.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	4184	4184	4184	4184	4184	
5°	4182	4170	4144	4113	4104	397
15°	4028	3984	3872	3794	3782	1138
25°	3679	3545	3324	3256	3251	1686
35°	2867	2744	2548	2523	2531	1784
45°	1862	1814	1730	1737	1744	1441
55°	1136	1081	1010	979	948	1023
65°	644	581	472	342	287	641
75°	271	212	101	55	56	293
85°	25	14	4	6	6	44
90°	0	0	0	0	0	



TEST NUMBER: P684652

CATALOG NUMBER: LX6C80D010 EX6C809035 6LBLWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7
2.5°	4193.5	4193.5	4193.5	4193.5	4193.5	4193.5	4192.1	4192.1	4189.3	4189.3	4187.9
5°	4182.3	4183.7	4183.7	4182.3	4182.3	4179.5	4179.5	4178.1	4173.8	4171.0	4169.6
7.5°	4158.4	4158.4	4157.0	4155.6	4154.2	4149.9	4148.5	4144.3	4141.5	4138.7	4133.1
10°	4121.8	4121.8	4120.4	4117.6	4116.2	4113.4	4113.4	4107.8	4102.1	4095.1	4090.9
12.5°	4078.2	4079.6	4076.8	4075.4	4071.2	4069.8	4067.0	4059.9	4055.7	4047.3	4040.3
15°	4027.6	4030.4	4030.4	4024.8	4020.6	4019.2	4014.9	4010.7	4000.9	3992.4	3984.0
17.5°	3978.4	3981.2	3978.4	3974.2	3969.9	3964.3	3961.5	3953.1	3940.4	3929.2	3916.5
20°	3909.5	3913.7	3908.1	3901.0	3892.6	3891.2	3887.0	3872.9	3854.6	3837.7	3819.5
22.5°	3812.4	3809.6	3805.4	3802.6	3788.5	3780.1	3774.5	3756.2	3736.5	3714.0	3691.5
25°	3678.8	3684.5	3676.0	3663.4	3656.3	3647.9	3633.8	3614.1	3595.9	3572.0	3545.2
27.5°	3521.3	3521.3	3510.1	3505.9	3490.4	3479.1	3472.1	3452.4	3428.5	3404.6	3375.1
30°	3339.9	3331.5	3331.5	3311.8	3299.1	3294.9	3287.9	3255.5	3234.5	3209.1	3179.6
32.5°	3120.5	3119.1	3113.5	3100.9	3084.0	3069.9	3069.9	3047.4	3019.3	2988.4	2970.1
35°	2867.4	2868.8	2866.0	2851.9	2851.9	2835.1	2832.3	2812.6	2790.1	2766.2	2743.7
37.5°	2605.8	2611.5	2605.8	2598.8	2594.6	2593.2	2580.5	2566.5	2549.6	2535.5	2518.7
40°	2352.7	2344.3	2347.1	2333.0	2334.4	2331.6	2326.0	2307.7	2297.9	2283.8	2265.5
42.5°	2079.9	2088.3	2091.1	2082.7	2079.9	2074.3	2079.9	2072.9	2061.6	2054.6	2037.7
45°	1861.9	1853.5	1857.7	1854.9	1856.3	1845.0	1840.8	1838.0	1833.8	1821.1	1814.1
47.5°	1645.4	1646.8	1645.4	1639.7	1636.9	1636.9	1631.3	1622.9	1622.9	1614.4	1608.8
50°	1456.9	1456.9	1459.7	1452.7	1449.9	1444.3	1445.7	1437.2	1431.6	1424.6	1420.3
52.5°	1283.9	1285.3	1279.7	1281.1	1278.3	1278.3	1272.7	1267.1	1261.4	1248.8	1246.0
55°	1136.3	1137.7	1130.7	1133.5	1125.0	1120.8	1118.0	1109.6	1109.6	1096.9	1081.4
57.5°	998.5	997.1	995.6	991.4	985.8	981.6	977.4	967.5	963.3	954.9	942.2
60°	870.5	869.1	866.3	864.9	860.6	850.8	850.8	843.8	829.7	821.3	808.6
62.5°	749.5	749.5	748.1	743.9	739.7	735.5	732.7	727.0	713.0	703.1	691.9
65°	644.1	642.7	638.5	631.4	628.6	628.6	618.8	614.5	603.3	593.5	580.8
67.5°	542.8	537.2	534.4	535.8	527.4	527.4	518.9	511.9	502.0	485.2	475.3
70°	444.4	441.6	438.8	435.9	434.5	428.9	424.7	416.3	406.4	393.8	378.3
72.5°	355.8	355.8	351.6	348.8	344.5	338.9	336.1	329.1	317.8	303.8	292.5
75°	271.4	271.4	271.4	265.8	263.0	260.2	251.7	247.5	234.8	226.4	212.3
77.5°	199.7	196.9	192.7	191.3	188.4	185.6	181.4	174.4	163.1	153.3	144.8
80°	126.6	130.8	126.6	126.6	119.5	116.7	115.3	106.9	102.7	94.2	87.2
82.5°	70.3	71.7	68.9	67.5	63.3	61.9	61.9	56.3	53.4	47.8	43.6
85°	25.3	26.7	25.3	25.3	22.5	23.9	22.5	21.1	18.3	15.5	14.1
87.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P684652

CATALOG NUMBER: LX6C80D010 EX6C809035 6LBLWWH

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7
2.5°	4187.9	4185.1	4185.1	4183.7	4182.3	4182.3	4182.3	4180.9	4178.1	4178.1	4176.7
5°	4166.8	4164.0	4159.8	4157.0	4155.6	4154.2	4152.8	4151.3	4145.7	4144.3	4140.1
7.5°	4128.8	4126.0	4119.0	4116.2	4112.0	4110.6	4104.9	4102.1	4096.5	4090.9	4088.1
10°	4083.8	4076.8	4071.2	4064.2	4061.3	4057.1	4050.1	4041.7	4037.4	4030.4	4024.8
12.5°	4033.2	4024.8	4013.5	4005.1	4002.3	3995.2	3984.0	3977.0	3967.1	3955.9	3946.0
15°	3969.9	3960.1	3950.2	3934.8	3930.6	3922.1	3910.9	3896.8	3882.7	3871.5	3860.2
17.5°	3901.0	3885.6	3870.1	3853.2	3840.6	3836.3	3818.1	3798.4	3785.7	3766.0	3753.4
20°	3804.0	3782.9	3757.6	3740.7	3729.5	3716.8	3695.7	3674.6	3659.1	3642.3	3624.0
22.5°	3670.4	3650.7	3621.2	3595.9	3587.4	3569.1	3550.9	3531.2	3511.5	3493.2	3470.7
25°	3512.9	3491.8	3462.3	3437.0	3422.9	3414.5	3379.3	3359.6	3339.9	3324.5	3309.0
27.5°	3351.2	3313.2	3293.5	3254.1	3241.5	3238.7	3206.3	3185.2	3164.1	3143.0	3123.4
30°	3151.5	3121.9	3092.4	3064.3	3047.4	3037.6	3013.7	2986.9	2972.9	2958.8	2939.1
32.5°	2944.8	2918.0	2881.5	2854.8	2842.1	2828.0	2806.9	2788.7	2767.6	2752.1	2747.9
35°	2724.0	2694.4	2663.5	2643.8	2641.0	2624.1	2603.0	2587.6	2572.1	2548.2	2544.0
37.5°	2487.7	2470.8	2449.7	2421.6	2409.0	2409.0	2387.9	2376.6	2356.9	2355.5	2344.3
40°	2255.7	2248.6	2216.3	2207.9	2205.1	2185.4	2179.7	2160.1	2146.0	2144.6	2127.7
42.5°	2026.5	2008.2	2002.5	1988.5	1975.8	1973.0	1960.4	1951.9	1946.3	1937.9	1929.4
45°	1798.6	1794.4	1780.4	1770.5	1766.3	1760.7	1756.4	1739.6	1736.8	1729.7	1725.5
47.5°	1601.8	1590.5	1577.8	1566.6	1565.2	1556.8	1546.9	1546.9	1531.4	1530.0	1527.2
50°	1406.3	1397.8	1390.8	1375.3	1378.2	1366.9	1365.5	1352.8	1345.8	1340.2	1347.2
52.5°	1234.7	1217.8	1215.0	1202.4	1198.2	1199.6	1184.1	1179.9	1177.1	1171.4	1168.6
55°	1071.6	1063.1	1051.9	1043.5	1036.4	1029.4	1023.8	1023.8	1008.3	1009.7	1002.7
57.5°	928.1	921.1	907.1	894.4	891.6	883.1	876.1	869.1	867.7	857.8	850.8
60°	800.2	787.5	769.2	763.6	755.2	748.1	741.1	732.7	728.5	721.4	708.8
62.5°	680.6	659.5	652.5	641.3	631.4	627.2	616.0	606.1	599.1	589.2	579.4
65°	566.7	551.3	538.6	525.9	524.5	513.3	503.4	495.0	480.9	472.5	454.2
67.5°	462.7	448.6	434.5	421.9	412.0	409.2	393.8	383.9	374.1	357.2	341.7
70°	367.0	353.0	341.7	326.3	322.0	310.8	299.5	289.7	272.8	257.3	244.7
72.5°	279.9	264.4	251.7	240.5	233.4	223.6	212.3	201.1	184.2	168.8	157.5
75°	199.7	188.4	175.8	164.5	158.9	153.3	140.6	128.0	116.7	101.3	91.4
77.5°	135.0	123.8	112.5	102.7	95.6	91.4	83.0	73.1	63.3	54.8	47.8
80°	78.8	71.7	63.3	54.8	53.4	49.2	42.2	36.6	30.9	26.7	21.1
82.5°	38.0	33.8	28.1	23.9	21.1	19.7	16.9	14.1	11.3	9.8	9.8
85°	11.3	9.8	8.4	7.0	5.6	5.6	4.2	4.2	4.2	4.2	4.2
87.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P684652

CATALOG NUMBER: LX6C80D010 EX6C809035 6LBLWWH

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7
2.5°	4172.4	4171.0	4169.6	4168.2	4165.4	4165.4	4161.2	4158.4	4158.4	4155.6	4154.2
5°	4135.9	4131.7	4130.3	4127.4	4124.6	4123.2	4117.6	4116.2	4113.4	4110.6	4110.6
7.5°	4083.8	4078.2	4072.6	4069.8	4068.4	4064.2	4061.3	4059.9	4055.7	4052.9	4047.3
10°	4014.9	4010.7	4003.7	4000.9	3998.1	3995.2	3988.2	3984.0	3982.6	3979.8	3977.0
12.5°	3934.8	3929.2	3922.1	3916.5	3913.7	3909.5	3902.4	3898.2	3898.2	3892.6	3892.6
15°	3849.0	3840.6	3827.9	3822.3	3820.9	3812.4	3806.8	3801.2	3794.2	3791.3	3791.3
17.5°	3739.3	3725.2	3714.0	3714.0	3708.4	3699.9	3691.5	3687.3	3683.1	3677.4	3674.6
20°	3609.9	3600.1	3587.4	3587.4	3574.8	3572.0	3563.5	3562.1	3552.3	3553.7	3549.5
22.5°	3453.8	3448.2	3441.2	3435.5	3428.5	3420.1	3415.9	3417.3	3413.0	3411.6	3410.2
25°	3296.3	3280.9	3272.4	3269.6	3266.8	3259.8	3257.0	3255.5	3255.5	3251.3	3252.7
27.5°	3114.9	3103.7	3092.4	3096.6	3091.0	3086.8	3084.0	3079.8	3082.6	3081.2	3082.6
30°	2929.3	2915.2	2908.2	2911.0	2909.6	2898.3	2904.0	2902.6	2904.0	2904.0	2906.8
32.5°	2733.8	2724.0	2722.6	2724.0	2711.3	2712.7	2707.1	2715.5	2716.9	2725.4	2718.3
35°	2535.5	2529.9	2520.1	2518.7	2520.1	2518.7	2518.7	2524.3	2522.9	2531.3	2528.5
37.5°	2331.6	2328.8	2319.0	2321.8	2316.1	2326.0	2328.8	2326.0	2335.8	2333.0	2331.6
40°	2131.9	2127.7	2122.1	2133.3	2126.3	2120.7	2130.5	2122.1	2124.9	2133.3	2133.3
42.5°	1929.4	1922.4	1922.4	1922.4	1921.0	1921.0	1925.2	1929.4	1926.6	1928.0	1939.3
45°	1725.5	1724.1	1719.9	1722.7	1721.3	1728.3	1728.3	1731.1	1736.8	1742.4	1739.6
47.5°	1528.6	1525.8	1530.0	1527.2	1528.6	1524.4	1527.2	1535.7	1542.7	1532.8	1542.7
50°	1344.4	1338.8	1337.4	1341.6	1340.2	1338.8	1341.6	1341.6	1338.8	1338.8	1348.6
52.5°	1168.6	1163.0	1158.8	1165.8	1161.6	1163.0	1157.4	1157.4	1160.2	1157.4	1153.2
55°	1004.1	999.9	994.2	997.1	990.0	988.6	983.0	983.0	978.8	976.0	967.5
57.5°	846.6	843.8	831.1	829.7	831.1	821.3	811.4	807.2	796.0	793.1	791.7
60°	707.4	691.9	684.9	676.4	670.8	666.6	655.3	648.3	631.4	621.6	620.2
62.5°	562.5	555.5	547.0	534.4	531.6	517.5	506.3	488.0	479.5	466.9	454.2
65°	445.8	427.5	414.9	407.8	396.6	383.9	371.3	351.6	341.7	326.3	313.6
67.5°	326.3	310.8	293.9	288.3	278.4	263.0	250.3	233.4	225.0	210.9	206.7
70°	223.6	209.5	196.9	188.4	181.4	165.9	153.3	147.7	139.2	136.4	136.4
72.5°	143.4	130.8	116.7	112.5	106.9	98.4	90.0	87.2	90.0	88.6	88.6
75°	80.2	73.1	63.3	59.1	59.1	56.3	54.8	54.8	54.8	54.8	54.8
77.5°	40.8	36.6	33.8	32.3	32.3	32.3	33.8	33.8	33.8	35.2	33.8
80°	19.7	18.3	18.3	18.3	19.7	19.7	19.7	19.7	19.7	21.1	19.7
82.5°	9.8	9.8	9.8	9.8	9.8	9.8	11.3	11.3	11.3	11.3	11.3
85°	4.2	4.2	4.2	4.2	5.6	5.6	5.6	5.6	5.6	5.6	5.6
87.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P684652

CATALOG NUMBER: LX6C80D010 EX6C809035 6LBLWWH

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7	4183.7
2.5°	4152.8	4149.9	4149.9	4148.5	4148.5	4148.5	4148.5	4149.9
5°	4107.8	4106.3	4106.3	4103.5	4103.5	4103.5	4103.5	4103.5
7.5°	4047.3	4044.5	4045.9	4043.1	4043.1	4044.5	4043.1	4041.7
10°	3972.7	3971.3	3972.7	3972.7	3969.9	3968.5	3969.9	3971.3
12.5°	3888.4	3887.0	3884.2	3885.6	3885.6	3884.2	3882.7	3879.9
15°	3789.9	3788.5	3787.1	3785.7	3784.3	3785.7	3784.3	3781.5
17.5°	3674.6	3674.6	3673.2	3671.8	3670.4	3667.6	3669.0	3673.2
20°	3550.9	3549.5	3546.6	3548.1	3542.4	3539.6	3541.0	3545.2
22.5°	3408.8	3404.6	3407.4	3403.2	3403.2	3404.6	3403.2	3400.4
25°	3254.1	3248.5	3251.3	3252.7	3252.7	3251.3	3249.9	3251.3
27.5°	3082.6	3086.8	3086.8	3084.0	3088.2	3082.6	3085.4	3086.8
30°	2906.8	2902.6	2901.2	2906.8	2915.2	2908.2	2908.2	2909.6
32.5°	2725.4	2719.8	2719.8	2722.6	2721.2	2721.2	2726.8	2719.8
35°	2531.3	2534.1	2522.9	2529.9	2532.7	2529.9	2531.3	2531.3
37.5°	2335.8	2333.0	2333.0	2333.0	2337.2	2337.2	2340.1	2338.6
40°	2143.2	2137.5	2136.1	2139.0	2133.3	2137.5	2137.5	2133.3
42.5°	1935.0	1936.5	1943.5	1936.5	1937.9	1936.5	1933.6	1932.2
45°	1742.4	1746.6	1743.8	1742.4	1743.8	1738.2	1739.6	1743.8
47.5°	1538.5	1546.9	1538.5	1544.1	1542.7	1539.9	1537.1	1531.4
50°	1347.2	1350.0	1348.6	1347.2	1345.8	1344.4	1337.4	1333.2
52.5°	1151.7	1151.7	1151.7	1151.7	1137.7	1144.7	1141.9	1133.5
55°	960.5	964.7	959.1	959.1	949.2	949.2	946.4	947.8
57.5°	776.3	772.0	767.8	767.8	758.0	753.8	749.5	743.9
60°	604.7	600.5	594.9	587.8	578.0	578.0	575.2	563.9
62.5°	443.0	435.9	431.7	426.1	417.7	412.0	407.8	410.6
65°	303.8	296.7	291.1	291.1	291.1	288.3	286.9	286.9
67.5°	199.7	203.9	201.1	203.9	203.9	201.1	199.7	202.5
70°	137.8	137.8	136.4	136.4	136.4	136.4	135.0	136.4
72.5°	88.6	88.6	88.6	90.0	88.6	88.6	90.0	90.0
75°	56.3	56.3	56.3	57.7	56.3	56.3	57.7	56.3
77.5°	33.8	35.2	35.2	35.2	35.2	33.8	35.2	35.2
80°	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1
82.5°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3
85°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
87.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°    - - 45°-225°    - - - - 90°-270°















(END OF REPORT)