

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P785994

Luminaire Tested: LERS6D08D010-EC6DR150210IC9035-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P785994
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D08D010-EC6DR150210IC9035-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 916.2 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P785994

CATALOG NUMBER: LERS6D08D010-EC6DR150210IC9035-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P785994

CATALOG NUMBER: LERS6D08D010-EC6DR150210IC9035-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1404497	1404497	1404497
5°	825349	814657	821101
10°	246323	248049	251847
15°	61269	62467	60539
20°	18328	21233	18721
25°	6466	8234	6544
30°	2374	3123	2411
35°	1191	1343	1155
40°	753	824	753
45°	553	595	553
50°	438	438	438
55°	369	369	369
60°	295	295	295
65°	228	228	228
70°	190	190	190
75°	121	121	159
80°	87	87	87
85°	42	42	42

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 595 cd/sqm



TEST NUMBER: P785994

CATALOG NUMBER: LERS6D08D010-EC6DR150210IC9035-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	594.2	64.9
10°-20°	244.4	26.7
20°-30°	48.5	5.3
30°-40°	12.1	1.3
40°-50°	6.4	0.7
50°-60°	4.7	0.5
60°-70°	3.3	0.4
70°-80°	1.9	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	887.1	96.8
0°-40°	899.2	98.2
0°-60°	910.3	99.4
0°-90°	916.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	916.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	12482	12482	12482	12482	12482	
5°	8121	8038	8016	8072	8079	593
15°	705	719	719	706	697	242
25°	83	94	106	94	84	44
35°	16	17	18	17	16	11
45°	8	8	8	8	8	6
55°	5	5	5	5	5	5
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	0	0	0	0	0	1
90°	0	0	0	0	0	



TEST NUMBER: P785994

CATALOG NUMBER: LERS6D08D010-EC6DR150210IC9035-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	12482.2	12482.2	12482.2	12482.2	12482.2
2.5°	11259.4	11268.9	11272.6	11283.7	11324.9
5°	8121.2	8037.7	8016.0	8071.5	8079.4
7.5°	4810.7	4827.6	4889.4	4903.1	4853.5
10°	2639.9	2661.6	2658.4	2677.5	2699.1
12.5°	1350.1	1333.2	1327.9	1349.6	1319.4
15°	705.4	718.6	719.2	706.5	697.0
17.5°	379.4	394.7	420.1	399.5	367.8
20°	224.0	237.8	259.5	242.5	228.8
22.5°	138.4	149.5	164.9	151.7	140.6
25°	83.0	94.1	105.7	93.5	84.0
27.5°	49.1	58.7	66.1	58.1	48.6
30°	31.7	37.0	41.7	36.5	32.2
32.5°	22.2	24.3	26.4	24.3	22.2
35°	16.4	17.4	18.5	17.4	15.9
37.5°	12.7	13.7	14.3	13.2	12.2
40°	10.6	11.1	11.6	11.1	10.6
42.5°	9.0	9.5	9.5	9.5	9.0
45°	7.9	7.9	8.5	7.9	7.9
47.5°	6.9	6.9	7.4	6.9	6.9
50°	6.3	6.3	6.3	6.3	6.3
52.5°	5.8	5.8	5.8	5.8	5.8
55°	5.3	5.3	5.3	5.3	5.3
57.5°	4.8	4.8	4.8	4.8	4.8
60°	4.2	4.2	4.2	4.2	4.2
62.5°	3.7	3.7	3.7	3.7	3.7
65°	3.2	3.2	3.2	3.2	3.2
67.5°	3.2	3.2	3.2	3.2	3.2
70°	2.6	2.6	2.6	2.6	2.6
72.5°	2.1	2.1	2.1	2.1	2.1
75°	1.6	1.6	1.6	1.6	2.1
77.5°	1.6	1.6	1.6	1.6	1.6
80°	1.1	1.1	1.1	1.1	1.1
82.5°	1.1	1.1	1.1	1.1	1.1
85°	0.5	0.5	0.5	0.5	0.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)