

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684663

Luminaire Tested: **LX6C80D010 EX6C809040 6LBSH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C80D010 EX6C809040 6LBSH
Description: 6 INCH 8000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9621.0 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 89.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684663

CATALOG NUMBER: LX6C80D010 EX6C809040 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684663

CATALOG NUMBER: LX6C80D010 EX6C809040 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	275844
5°	274559
10°	268888
15°	259110
20°	247197
25°	233874
30°	220610
35°	207723
40°	195588
45°	182321
50°	166238
55°	146814
60°	124266
65°	97572
70°	69627
75°	38147
80°	6724
85°	0



TEST NUMBER: P684663

CATALOG NUMBER: LX6C80D010 EX6C809040 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	471.3	4.9
10°-20°	1281.0	13.3
20°-30°	1779.0	18.5
30°-40°	1941.4	20.2
40°-50°	1811.0	18.8
50°-60°	1374.6	14.3
60°-70°	752.7	7.8
70°-80°	207.1	2.2
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3531.3	36.7
0°-40°	5472.7	56.9
0°-60°	8658.3	90.0
0°-90°	9621.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9621.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5032	
5°	4989	471
15°	4566	1281
25°	3866	1779
35°	3104	1941
45°	2352	1811
55°	1536	1375
65°	752	753
75°	180	207
85°	0	3
90°	0	



TEST NUMBER: P684663

CATALOG NUMBER: LX6C80D010 EX6C809040 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5031.8
2.5°	5031.8
5°	4989.3
7.5°	4925.7
10°	4830.4
12.5°	4703.3
15°	4565.5
17.5°	4396.1
20°	4237.3
22.5°	4046.6
25°	3866.5
27.5°	3686.4
30°	3485.1
32.5°	3294.3
35°	3103.9
37.5°	2913.2
40°	2733.1
42.5°	2542.4
45°	2351.7
47.5°	2160.9
50°	1949.2
52.5°	1747.8
55°	1536.1
57.5°	1334.8
60°	1133.4
62.5°	932.3
65°	752.2
67.5°	582.5
70°	434.4
72.5°	296.6
75°	180.1
77.5°	84.8
80°	21.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)