

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856677

Luminaire Tested: **LD6C80D010 EU6809050 6LBWLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P856677
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C80D010 EU6809050 6LBWLI
Description: 6 INCH 8000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9526.0 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 89.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856677

CATALOG NUMBER: LD6C80D010 EU6809050 6LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P856677

CATALOG NUMBER: LD6C80D010 EU6809050 6LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76	76	76	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69	69	69	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63	63	63	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57	57	57	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52	52	52	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48	48	48	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	326240
5°	329264
10°	338476
15°	346943
20°	352212
25°	344935
30°	323385
35°	289128
40°	234189
45°	154915
50°	78300
55°	33041
60°	10646
65°	4177
70°	3478
75°	2309
80°	0
85°	0



TEST NUMBER: P856677

CATALOG NUMBER: LD6C80D010 EU6809050 6LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	574.1	6.0
10°-20°	1725.6	18.1
20°-30°	2601.2	27.3
30°-40°	2662.4	27.9
40°-50°	1551.0	16.3
50°-60°	356.4	3.7
60°-70°	43.7	0.5
70°-80°	11.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4900.9	51.4
0°-40°	7563.3	79.4
0°-60°	9470.8	99.4
0°-90°	9526.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9526.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5951	
5°	5983	574
15°	6113	1726
25°	5703	2601
35°	4320	2662
45°	1998	1551
55°	346	356
65°	32	44
75°	11	11
85°	0	0
90°	0	



TEST NUMBER: P856677

CATALOG NUMBER: LD6C80D010 EU6809050 6LBWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5951.1
2.5°	5940.3
5°	5983.4
7.5°	6026.5
10°	6080.5
12.5°	6091.3
15°	6113.1
17.5°	6091.3
20°	6037.4
22.5°	5864.5
25°	5702.6
27.5°	5443.5
30°	5108.7
32.5°	4763.1
35°	4320.3
37.5°	3823.2
40°	3272.5
42.5°	2656.9
45°	1998.2
47.5°	1393.1
50°	918.1
52.5°	583.3
55°	345.7
57.5°	183.7
60°	97.1
62.5°	54.0
65°	32.2
67.5°	32.2
70°	21.7
72.5°	10.9
75°	10.9
77.5°	10.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)