

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685258

Luminaire Tested: **LX6C80D010 EX6809050 6LBNLI**

Issue Date: 2/14/2022

Test Information

Test Method: LM-79-08
Report Number: P685258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C80D010 EX6809050 6LBNLI
Description: 6 INCH 8000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7495.0 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 89.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685258
CATALOG NUMBER: LX6C80D010 EX6809050 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685258

CATALOG NUMBER: LX6C80D010 EX6809050 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	935468
5°	874822
10°	713486
15°	525031
20°	361885
25°	268661
30°	201803
35°	125842
40°	61086
45°	20956
50°	2746
55°	2074
60°	1195
65°	1414
70°	1747
75°	0
80°	0
85°	0



TEST NUMBER: P685258

CATALOG NUMBER: LX6C80D010 EX6809050 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1418.8	18.9
10°-20°	2546.6	34.0
20°-30°	2059.0	27.5
30°-40°	1186.1	15.8
40°-50°	250.7	3.3
50°-60°	21.6	0.3
60°-70°	10.8	0.1
70°-80°	1.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6024.3	80.4
0°-40°	7210.4	96.2
0°-60°	7482.8	99.8
0°-90°	7495.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7495.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17064	
5°	15897	###
15°	9251	2547
25°	4442	2059
35°	1880	1186
45°	270	251
55°	22	22
65°	11	11
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685258

CATALOG NUMBER: LX6C80D010 EX6809050 6LBNLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	17064.3
2.5°	16859.3
5°	15897.3
7.5°	14514.0
10°	12817.3
12.5°	11077.5
15°	9251.0
17.5°	7489.4
20°	6203.2
22.5°	5219.9
25°	4441.6
27.5°	3782.6
30°	3188.0
32.5°	2529.0
35°	1880.4
37.5°	1307.6
40°	853.6
42.5°	518.8
45°	270.3
47.5°	108.0
50°	32.2
52.5°	32.2
55°	21.7
57.5°	21.7
60°	10.9
62.5°	10.9
65°	10.9
67.5°	10.9
70°	10.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)