

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786072

Luminaire Tested: LERS6D08D010-EC6DR300210IC9050-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D08D010-EC6DR300210IC9050-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1402.0 lumens
Efficiency: N/A
Efficacy: 157.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786072

CATALOG NUMBER: LERS6D08D010-EC6DR300210IC9050-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P786072

CATALOG NUMBER: LERS6D08D010-EC6DR300210IC9050-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	345058	345058	345058
5°	335158	334766	335173
10°	290292	288248	290222
15°	189400	188386	187435
20°	94179	97714	94057
25°	47439	53495	46468
30°	18994	20700	16546
35°	8812	8438	7074
40°	3807	4227	3587
45°	2685	3334	2706
50°	917	2429	976
55°	534	1001	560
60°	367	444	367
65°	235	235	235
70°	157	90	157
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 3334 cd/sqm



TEST NUMBER: P786072

CATALOG NUMBER: LERS6D08D010-EC6DR300210IC9050-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	396.4	28.3
10°-20°	638.4	45.5
20°-30°	275.9	19.7
30°-40°	62.9	4.5
40°-50°	21.6	1.5
50°-60°	5.3	0.4
60°-70°	1.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1310.7	93.5
0°-40°	1373.6	98.0
0°-60°	1400.5	99.9
0°-90°	1402.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1402.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4508	4508	4508	4508	4508	
5°	4362	4358	4357	4366	4362	397
15°	2390	2361	2377	2370	2365	640
25°	562	583	633	568	550	269
35°	94	96	90	90	76	64
45°	25	31	31	31	25	18
55°	4	4	8	4	4	4
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P786072

CATALOG NUMBER: LERS6D08D010-EC6DR300210IC9050-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4508.0	4508.0	4508.0	4508.0	4508.0
2.5°	4478.2	4475.1	4476.8	4479.0	4479.9
5°	4362.0	4357.8	4356.9	4365.9	4362.2
7.5°	4127.6	4121.6	4112.5	4133.1	4152.4
10°	3734.9	3728.3	3708.6	3718.3	3734.0
12.5°	3155.3	3133.8	3133.4	3164.3	3160.1
15°	2390.1	2361.4	2377.3	2369.6	2365.3
17.5°	1607.3	1596.2	1617.5	1611.1	1583.4
20°	1156.2	1159.1	1199.6	1179.2	1154.7
22.5°	843.7	854.1	902.1	849.7	830.4
25°	561.7	583.0	633.4	568.2	550.2
27.5°	345.5	355.2	406.4	341.1	331.3
30°	214.9	210.0	234.2	201.0	187.2
32.5°	141.0	134.8	142.5	127.9	116.9
35°	94.3	96.3	90.3	89.6	75.7
37.5°	58.9	67.7	59.8	63.7	48.7
40°	38.1	49.1	42.3	46.7	35.9
42.5°	31.2	37.8	34.7	37.0	31.9
45°	24.8	30.8	30.8	30.8	25.0
47.5°	13.7	20.6	26.3	21.0	14.6
50°	7.7	10.4	20.4	10.8	8.2
52.5°	5.3	6.0	13.9	6.2	5.5
55°	4.0	4.2	7.5	4.4	4.2
57.5°	3.1	3.3	4.0	3.3	3.1
60°	2.4	2.4	2.9	2.7	2.4
62.5°	1.8	1.8	2.0	1.8	1.8
65°	1.3	1.3	1.3	1.3	1.3
67.5°	0.7	0.9	0.9	0.9	0.9
70°	0.7	0.4	0.4	0.4	0.7
72.5°	0.4	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)