

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786120

Luminaire Tested: LERS6D08D010-EC6DR400210IC9050-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D08D010-EC6DR400210IC9050-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1501.2 lumens
Efficiency: N/A
Efficacy: 168.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786120

CATALOG NUMBER: LERS6D08D010-EC6DR400210IC9050-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P786120

CATALOG NUMBER: LERS6D08D010-EC6DR400210IC9050-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|-----|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | 100 | | | | | | | | | | | | | |
| 1 | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 | 103 | 101 | 100 | 99 | 98 | 97 | 96 | | | | | | 96 | | | | | | | | | | | | | |
| 2 | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 99 | 102 | 99 | 97 | 99 | 97 | 95 | 96 | 95 | 93 | 92 | | | | | | 92 | | | | | | | | | | | | | |
| 3 | 106 | 101 | 97 | 94 | 104 | 100 | 96 | 93 | 97 | 94 | 92 | 95 | 93 | 90 | 93 | 91 | 89 | 88 | | | | | | 88 | | | | | | | | | | | | | |
| 4 | 102 | 97 | 92 | 89 | 101 | 95 | 91 | 88 | 93 | 90 | 87 | 92 | 89 | 86 | 90 | 87 | 85 | 84 | | | | | | 84 | | | | | | | | | | | | | |
| 5 | 99 | 92 | 88 | 84 | 97 | 91 | 87 | 84 | 90 | 86 | 83 | 88 | 85 | 83 | 87 | 84 | 82 | 81 | | | | | | 81 | | | | | | | | | | | | | |
| 6 | 95 | 88 | 84 | 80 | 94 | 88 | 83 | 80 | 86 | 82 | 80 | 85 | 82 | 79 | 84 | 81 | 79 | 77 | | | | | | 77 | | | | | | | | | | | | | |
| 7 | 92 | 85 | 80 | 77 | 91 | 84 | 80 | 77 | 83 | 79 | 76 | 82 | 79 | 76 | 81 | 78 | 76 | 74 | | | | | | 74 | | | | | | | | | | | | | |
| 8 | 89 | 82 | 77 | 74 | 88 | 81 | 77 | 74 | 80 | 76 | 73 | 79 | 76 | 73 | 78 | 75 | 73 | 72 | | | | | | 72 | | | | | | | | | | | | | |
| 9 | 86 | 79 | 74 | 71 | 85 | 78 | 74 | 71 | 77 | 73 | 71 | 77 | 73 | 70 | 76 | 72 | 70 | 69 | | | | | | 69 | | | | | | | | | | | | | |
| 10 | 83 | 76 | 71 | 68 | 82 | 75 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 73 | 70 | 68 | 67 | | | | | | 67 | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 381888 |
| 5° | 380035 |
| 10° | 359211 |
| 15° | 305377 |
| 20° | 208140 |
| 25° | 86848 |
| 30° | 27302 |
| 35° | 12685 |
| 40° | 7017 |
| 45° | 3214 |
| 50° | 1564 |
| 55° | 857 |
| 60° | 437 |
| 65° | 155 |
| 70° | 64 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3214 cd/sqm



TEST NUMBER: P786120

CATALOG NUMBER: LERS6D08D010-EC6DR400210IC9050-6LBS1B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 323.5 | 21.6 |
| 10°-20° | 724.8 | 48.3 |
| 20°-30° | 362.8 | 24.2 |
| 30°-40° | 66.5 | 4.4 |
| 40°-50° | 18.4 | 1.2 |
| 50°-60° | 4.3 | 0.3 |
| 60°-70° | 0.8 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1411.2 | 94.0 |
| 0°-40° | 1477.7 | 98.4 |
| 0°-60° | 1500.4 | 99.9 |
| 0°-90° | 1501.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1501.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3495 | |
| 5° | 3465 | 324 |
| 15° | 2700 | 725 |
| 25° | 720 | 363 |
| 35° | 95 | 67 |
| 45° | 21 | 18 |
| 55° | 4 | 4 |
| 65° | 1 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P786120

CATALOG NUMBER: LERS6D08D010-EC6DR400210IC9050-6LBS1B

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 3495.2 |
| 2.5° | 3490.1 |
| 5° | 3465.0 |
| 7.5° | 3385.0 |
| 10° | 3237.7 |
| 12.5° | 3008.2 |
| 15° | 2699.7 |
| 17.5° | 2298.5 |
| 20° | 1790.1 |
| 22.5° | 1220.4 |
| 25° | 720.4 |
| 27.5° | 380.8 |
| 30° | 216.4 |
| 32.5° | 139.9 |
| 35° | 95.1 |
| 37.5° | 68.0 |
| 40° | 49.2 |
| 42.5° | 33.7 |
| 45° | 20.8 |
| 47.5° | 13.3 |
| 50° | 9.2 |
| 52.5° | 6.5 |
| 55° | 4.5 |
| 57.5° | 2.9 |
| 60° | 2.0 |
| 62.5° | 1.2 |
| 65° | 0.6 |
| 67.5° | 0.4 |
| 70° | 0.2 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)