

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685272

Luminaire Tested: **LX6C90D010 EX6909035 6LBMLI**

Issue Date: 2/15/2022



**Test Information**


Test Method: LM-79-08  
Report Number: P685272  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C90D010 EX6909035 6LBMLI  
Description: 6 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 6LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8788.0 lumens  
Efficiency: N/A  
Efficacy: 90.5 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 97.1  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685272  
CATALOG NUMBER: LX6C90D010 EX6909035 6LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685272

CATALOG NUMBER: LX6C90D010 EX6909035 6LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	602901
5°	597164
10°	565866
15°	513754
20°	453978
25°	392478
30°	306794
35°	188141
40°	96567
45°	38368
50°	12460
55°	4291
60°	3684
65°	2945
70°	1811
75°	2393
80°	0
85°	0



TEST NUMBER: P685272

CATALOG NUMBER: LX6C90D010 EX6909035 6LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1013.1	11.5
10°-20°	2522.3	28.7
20°-30°	2932.1	33.4
30°-40°	1795.5	20.4
40°-50°	445.9	5.1
50°-60°	52.1	0.6
60°-70°	19.5	0.2
70°-80°	7.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6467.6	73.6
0°-40°	8263.1	94.0
0°-60°	8761.1	99.7
0°-90°	8788.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8788.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10998	
5°	10852	###
15°	9052	2522
25°	6489	2932
35°	2811	1796
45°	495	446
55°	45	52
65°	23	19
75°	11	7
85°	0	0
90°	0	



TEST NUMBER: P685272

CATALOG NUMBER: LX6C90D010 EX6909035 6LBMLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10997.8
2.5°	10986.4
5°	10851.7
7.5°	10559.1
10°	10165.4
12.5°	9648.3
15°	9052.3
17.5°	8411.4
20°	7781.8
22.5°	7151.8
25°	6488.6
27.5°	5723.9
30°	4846.6
32.5°	3823.3
35°	2811.3
37.5°	1979.0
40°	1349.4
42.5°	843.2
45°	494.9
47.5°	281.2
50°	146.1
52.5°	67.6
55°	44.9
57.5°	33.6
60°	33.6
62.5°	22.7
65°	22.7
67.5°	11.3
70°	11.3
72.5°	11.3
75°	11.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)