

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856681

Luminaire Tested: **LD6C90D010 EU6909040 6LBWLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P856681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C90D010 EU6909040 6LBWLI
Description: 6 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9940.9 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856681

CATALOG NUMBER: LD6C90D010 EU6909040 6LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P856681

CATALOG NUMBER: LD6C90D010 EU6909040 6LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76	76	76	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69	69	69	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63	63	63	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57	57	57	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52	52	52	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48	48	48	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	340455
5°	343605
10°	353222
15°	362057
20°	367555
25°	359960
30°	337476
35°	301723
40°	244394
45°	161668
50°	81712
55°	34474
60°	11107
65°	4358
70°	3638
75°	2393
80°	0
85°	0



TEST NUMBER: P856681

CATALOG NUMBER: LD6C90D010 EU6909040 6LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	599.1	6.0
10°-20°	1800.7	18.1
20°-30°	2714.5	27.3
30°-40°	2778.4	27.9
40°-50°	1618.6	16.3
50°-60°	372.0	3.7
60°-70°	45.6	0.5
70°-80°	11.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5114.4	51.4
0°-40°	7892.8	79.4
0°-60°	9883.4	99.4
0°-90°	9940.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9940.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6210	
5°	6244	599
15°	6379	1801
25°	5951	2715
35°	4508	2778
45°	2085	1619
55°	361	372
65°	34	46
75°	11	12
85°	0	0
90°	0	



TEST NUMBER: P856681

CATALOG NUMBER: LD6C90D010 EU6909040 6LBWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6210.4
2.5°	6199.1
5°	6244.0
7.5°	6289.0
10°	6345.4
12.5°	6356.7
15°	6379.4
17.5°	6356.7
20°	6300.4
22.5°	6120.0
25°	5951.0
27.5°	5680.7
30°	5331.3
32.5°	4970.6
35°	4508.5
37.5°	3989.8
40°	3415.1
42.5°	2772.7
45°	2085.3
47.5°	1453.8
50°	958.1
52.5°	608.8
55°	360.7
57.5°	191.7
60°	101.3
62.5°	56.3
65°	33.6
67.5°	33.6
70°	22.7
72.5°	11.3
75°	11.3
77.5°	11.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)