

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786290

Luminaire Tested: LERS6D10D010-EC6DR100210IC9050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D10D010-EC6DR100210IC9050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1219.1 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786290

CATALOG NUMBER: LERS6D10D010-EC6DR100210IC9050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P786290

CATALOG NUMBER: LERS6D10D010-EC6DR100210IC9050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98						98													
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	99	98	97	96						97													
3	111	107	104	102	109	106	103	101	103	101	99	101	99	98	97	96	95	94						95													
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	96	95	94	93						94													
5	106	102	99	96	105	101	98	96	99	97	95	98	96	94	94	93	92	91						93													
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	93	92	91	90						91													
7	103	98	95	93	102	97	94	92	96	94	92	95	93	92	92	91	90	89						90													
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	90	89	88	87						89													
9	100	95	92	90	99	94	92	90	94	91	90	93	91	89	89	88	87	86						88													
10	98	94	91	89	98	93	91	89	93	90	88	92	90	88	88	87	86	85						88													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2900261
5°	1375298
10°	282059
15°	77439
20°	31208
25°	16721
30°	9891
35°	6442
40°	4307
45°	2797
50°	1530
55°	1143
60°	656
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2797 cd/sqm



TEST NUMBER: P786290

CATALOG NUMBER: LERS6D10D010-EC6DR100210IC9050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	866.9	71.1
10°-20°	234.6	19.2
20°-30°	67.2	5.5
30°-40°	30.7	2.5
40°-50°	14.1	1.2
50°-60°	4.7	0.4
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1168.6	95.9
0°-40°	1199.3	98.4
0°-60°	1218.0	99.9
0°-90°	1219.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1219.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26544	
5°	12539	867
15°	685	235
25°	139	67
35°	48	31
45°	18	14
55°	6	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P786290

CATALOG NUMBER: LERS6D10D010-EC6DR100210IC9050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	26544.4
0.5°	26315.2
1°	25727.2
1.5°	24593.3
2°	23323.6
2.5°	21646.9
3°	19783.2
3.5°	17979.8
4°	16034.6
4.5°	14243.3
5°	12539.4
5.5°	10995.3
6°	9523.7
6.5°	8229.9
7°	7011.6
7.5°	5971.1
8°	5048.3
8.5°	4240.1
9°	3540.5
9.5°	3006.7
10°	2542.3
12.5°	1212.3
15°	684.6
17.5°	416.2
20°	268.4
22.5°	187.0
25°	138.7
27.5°	102.5
30°	78.4
32.5°	60.3
35°	48.3
37.5°	36.2
40°	30.2
42.5°	24.1
45°	18.1
47.5°	12.1
50°	9.0
52.5°	6.0
55°	6.0
57.5°	3.0
60°	3.0
62.5°	3.0
65°	0.0



TEST NUMBER: P786290

CATALOG NUMBER: LERS6D10D010-EC6DR100210IC9050-6LBS1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.0
70°		0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)