

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P786293

Luminaire Tested: LERS6D10D010-EC6DR150210IC9024-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P786293
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS6D10D010-EC6DR150210IC9024-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 964.0 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P786293

CATALOG NUMBER: LERS6D10D010-EC6DR150210IC9024-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P786293

CATALOG NUMBER: LERS6D10D010-EC6DR150210IC9024-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1477826	1477826	1477826
5°	868439	857199	863978
10°	259190	261009	265003
15°	64474	65725	63701
20°	19286	22338	19695
25°	6801	8663	6886
30°	2501	3287	2538
35°	1249	1416	1213
40°	788	866	788
45°	581	623	581
50°	466	466	466
55°	390	390	390
60°	309	309	309
65°	236	236	236
70°	205	205	205
75°	128	128	166
80°	87	87	87
85°	50	50	50

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 623 cd/sqm



TEST NUMBER: P786293

CATALOG NUMBER: LERS6D10D010-EC6DR150210IC9024-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	625.2	64.9
10°-20°	257.2	26.7
20°-30°	51.1	5.3
30°-40°	12.7	1.3
40°-50°	6.7	0.7
50°-60°	5.0	0.5
60°-70°	3.5	0.4
70°-80°	2.0	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	933.4	96.8
0°-40°	946.2	98.2
0°-60°	957.9	99.4
0°-90°	964.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	964.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	13134	13134	13134	13134	13134	
5°	8545	8457	8435	8493	8501	624
15°	742	756	757	743	733	254
25°	87	99	111	98	88	46
35°	17	18	20	18	17	12
45°	8	8	9	8	8	7
55°	6	6	6	6	6	5
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P786293

CATALOG NUMBER: LERS6D10D010-EC6DR150210IC9024-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	13133.9	13133.9	13133.9	13133.9	13133.9
2.5°	11847.3	11857.3	11861.2	11872.9	11916.3
5°	8545.2	8457.4	8434.6	8493.0	8501.3
7.5°	5061.9	5079.6	5144.7	5159.2	5106.9
10°	2777.8	2800.6	2797.3	2817.3	2840.1
12.5°	1420.6	1402.8	1397.2	1420.0	1388.3
15°	742.3	756.2	756.7	743.4	733.4
17.5°	399.2	415.3	442.0	420.3	387.0
20°	235.7	250.2	273.0	255.2	240.7
22.5°	145.7	157.3	173.5	159.6	147.9
25°	87.3	99.0	111.2	98.4	88.4
27.5°	51.7	61.7	69.5	61.2	51.2
30°	33.4	38.9	43.9	38.4	33.9
32.5°	23.4	25.6	27.8	25.6	23.4
35°	17.2	18.3	19.5	18.3	16.7
37.5°	13.3	14.5	15.0	13.9	12.8
40°	11.1	11.7	12.2	11.7	11.1
42.5°	9.5	10.0	10.0	10.0	9.5
45°	8.3	8.3	8.9	8.3	8.3
47.5°	7.2	7.2	7.8	7.2	7.2
50°	6.7	6.7	6.7	6.7	6.7
52.5°	6.1	6.1	6.1	6.1	6.1
55°	5.6	5.6	5.6	5.6	5.6
57.5°	5.0	5.0	5.0	5.0	5.0
60°	4.4	4.4	4.4	4.4	4.4
62.5°	3.9	3.9	3.9	3.9	3.9
65°	3.3	3.3	3.3	3.3	3.3
67.5°	3.3	3.3	3.3	3.3	3.3
70°	2.8	2.8	2.8	2.8	2.8
72.5°	2.2	2.2	2.2	2.2	2.2
75°	1.7	1.7	1.7	1.7	2.2
77.5°	1.7	1.7	1.7	1.7	1.7
80°	1.1	1.1	1.1	1.1	1.1
82.5°	1.1	1.1	1.1	1.1	1.1
85°	0.6	0.6	0.6	0.6	0.6
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)