

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P133464

Luminaire Tested: **LD6A10D010TE ERN6A10927 6LN1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P133464
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23397)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A10D010TE ERN6A10927 6LN1LI
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 2700K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1008.8 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.49
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P133464

CATALOG NUMBER: LD6A10D010TE ERN6A10927 6LN1LI

Luminous Intensity Polar Plot





TEST NUMBER: P133464

CATALOG NUMBER: LD6A10D010TE ERN6A10927 6LN1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95				95
2	109	105	102	99	107	103	100	97	100	98	95	97	95	93	95	93	91	90				90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	87	85				85
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81				81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76				76
6	92	85	79	76	91	84	79	75	82	78	75	81	77	74	80	77	74	73				73
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	70	69				69
8	85	77	72	68	84	76	71	68	75	71	68	74	70	68	74	70	67	66				66
9	82	74	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63				63
10	79	70	65	62	78	70	65	62	69	65	62	69	65	62	68	64	62	60				60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	191834
5°	166514
10°	116515
15°	79382
20°	55993
25°	41233
30°	31632
35°	20700
40°	8985
45°	2869
50°	863
55°	239
60°	183
65°	108
70°	134
75°	0
80°	0
85°	0



TEST NUMBER: P133464

CATALOG NUMBER: LD6A10D010TE ERN6A10927 6LN1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.0	21.5
10°-20°	331.0	32.8
20°-30°	267.0	26.5
30°-40°	159.8	15.8
40°-50°	30.6	3.0
50°-60°	2.5	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	815.1	80.8
0°-40°	974.9	96.6
0°-60°	1008.0	99.9
0°-90°	1008.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1008.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2940	
5°	2543	217
15°	1175	331
25°	573	267
35°	260	160
45°	31	31
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P133464

CATALOG NUMBER: LD6A10D010TE ERN6A10927 6LN1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2940.4
2.5°	2830.7
5°	2542.6
7.5°	2152.4
10°	1758.8
12.5°	1429.5
15°	1175.3
17.5°	974.3
20°	806.5
22.5°	676.2
25°	572.8
27.5°	489.9
30°	419.9
32.5°	345.5
35°	259.9
37.5°	174.9
40°	105.5
42.5°	58.8
45°	31.1
47.5°	16.2
50°	8.5
52.5°	2.8
55°	2.1
57.5°	1.4
60°	1.4
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)