

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P135285

Luminaire Tested: **LD6A10D010TE ERM6A10930 6LM1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P135285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23398)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A10D010TE ERM6A10930 6LM1LI
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1098.8 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.8
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P135285

CATALOG NUMBER: LD6A10D010TE ERM6A10930 6LM1LI

Luminous Intensity Polar Plot





TEST NUMBER: P135285

CATALOG NUMBER: LD6A10D010TE ERM6A10930 6LM1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94			
2	109	104	101	98	107	103	99	96	99	97	94	97	94	92	94	92	90	89			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84			
4	99	92	87	83	98	91	87	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	72	69	85	77	72	68	76	71	68	75	71	68	74	70	67	66			
8	83	74	69	65	82	73	68	65	72	68	64	71	67	64	71	67	64	63			
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59			
10	76	67	62	58	75	67	61	58	66	61	58	65	61	58	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98859
5°	100304
10°	100828
15°	91742
20°	74746
25°	58409
30°	42089
35°	22484
40°	7827
45°	2122
50°	680
55°	330
60°	196
65°	108
70°	134
75°	176
80°	0
85°	0



TEST NUMBER: P135285

CATALOG NUMBER: LD6A10D010TE ERM6A10930 6LM1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.1	13.3
10°-20°	372.0	33.9
20°-30°	369.8	33.7
30°-40°	182.0	16.6
40°-50°	24.5	2.2
50°-60°	2.9	0.3
60°-70°	1.0	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	888.0	80.8
0°-40°	1070.0	97.4
0°-60°	1097.4	99.9
0°-90°	1098.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1098.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1515	
5°	1532	146
15°	1358	372
25°	811	370
35°	282	182
45°	23	24
55°	3	3
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P135285

CATALOG NUMBER: LD6A10D010TE ERM6A10930 6LM1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1515.3
2.5°	1514.6
5°	1531.6
7.5°	1542.7
10°	1522.0
12.5°	1460.5
15°	1358.3
17.5°	1224.2
20°	1076.6
22.5°	938.1
25°	811.4
27.5°	688.4
30°	558.7
32.5°	419.4
35°	282.3
37.5°	169.6
40°	91.9
42.5°	47.5
45°	23.0
47.5°	11.1
50°	6.7
52.5°	3.7
55°	2.9
57.5°	2.2
60°	1.5
62.5°	1.5
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)