

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P135196

Luminaire Tested: **LD6A15D010TE ERN6A15927 6LN1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P135196  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23370)  
Test Lab: INNOVATION CENTER P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6A15D010TE ERN6A15927 6LN1H  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: (1) HIGH LUMEN LED 2700K  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1155.0 lumens  
Efficiency: N/A  
Efficacy: 51.1 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.84  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 22.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P135196

CATALOG NUMBER: LD6A15D010TE ERN6A15927 6LN1H

### Luminous Intensity Polar Plot





TEST NUMBER: P135196

CATALOG NUMBER: LD6A15D010TE ERN6A15927 6LN1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70			
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54			
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	99381
5°	96133
10°	85704
15°	74702
20°	64693
25°	55508
30°	46594
35°	32694
40°	17025
45°	8101
50°	4253
55°	2309
60°	1592
65°	1034
70°	782
75°	681
80°	526
85°	0



TEST NUMBER: P135196

CATALOG NUMBER: LD6A15D010TE ERN6A15927 6LN1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.4	11.6
10°-20°	309.0	26.8
20°-30°	353.6	30.6
30°-40°	251.9	21.8
40°-50°	76.2	6.6
50°-60°	19.8	1.7
60°-70°	7.3	0.6
70°-80°	2.5	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.1	69.0
0°-40°	1049.0	90.8
0°-60°	1144.9	99.1
0°-90°	1155.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1155.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1523	
5°	1468	134
15°	1106	309
25°	771	354
35°	410	252
45°	88	76
55°	20	20
65°	7	7
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P135196

CATALOG NUMBER: LD6A15D010TE ERN6A15927 6LN1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1523.3
2.5°	1505.7
5°	1467.9
7.5°	1392.3
10°	1293.7
12.5°	1195.1
15°	1106.0
17.5°	1019.5
20°	931.8
22.5°	849.4
25°	771.1
27.5°	696.8
30°	618.5
32.5°	524.0
35°	410.5
37.5°	294.4
40°	199.9
42.5°	132.3
45°	87.8
47.5°	60.8
50°	41.9
52.5°	27.0
55°	20.3
57.5°	14.8
60°	12.2
62.5°	9.5
65°	6.7
67.5°	5.4
70°	4.1
72.5°	2.7
75°	2.7
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)