

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P136092

Luminaire Tested: **LD6A30D010TE ERW6A30927 6LW1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P136092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23358)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A30D010TE ERW6A30927 6LW1LI
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 2700K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2588.4 lumens
Efficiency: N/A
Efficacy: 57.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.12
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 45.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P136092

CATALOG NUMBER: LD6A30D010TE ERW6A30927 6LW1LI

Luminous Intensity Polar Plot





TEST NUMBER: P136092

CATALOG NUMBER: LD6A30D010TE ERW6A30927 6LW1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65	65	65	65
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59	59	59	59
7	79	68	62	57	77	68	61	57	66	61	57	65	60	56	64	59	56	54	54	54	54
8	74	64	57	53	73	63	57	52	62	56	52	61	56	52	60	55	52	50	50	50	50
9	70	60	53	49	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108763
5°	111536
10°	119145
15°	128654
20°	130746
25°	122727
30°	108096
35°	88047
40°	63942
45°	41030
50°	21568
55°	7371
60°	2114
65°	556
70°	343
75°	454
80°	0
85°	0



TEST NUMBER: P136092

CATALOG NUMBER: LD6A30D010TE ERW6A30927 6LW1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.7	6.4
10°-20°	534.3	20.6
20°-30°	775.2	30.0
30°-40°	682.9	26.4
40°-50°	349.6	13.5
50°-60°	73.7	2.8
60°-70°	5.7	0.2
70°-80°	1.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1475.2	57.0
0°-40°	2158.1	83.4
0°-60°	2581.5	99.7
0°-90°	2588.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2588.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1667	
5°	1703	166
15°	1905	534
25°	1705	775
35°	1106	683
45°	445	350
55°	65	74
65°	4	6
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P136092

CATALOG NUMBER: LD6A30D010TE ERW6A30927 6LW1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1667.1
2.5°	1670.7
5°	1703.1
7.5°	1748.1
10°	1798.5
12.5°	1856.1
15°	1904.8
17.5°	1917.4
20°	1883.2
22.5°	1807.6
25°	1704.9
27.5°	1580.7
30°	1434.9
32.5°	1274.6
35°	1105.5
37.5°	929.0
40°	750.8
42.5°	590.5
45°	444.7
47.5°	318.6
50°	212.5
52.5°	124.3
55°	64.8
57.5°	32.4
60°	16.2
62.5°	7.2
65°	3.6
67.5°	3.6
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)