

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P136209

Luminaire Tested: **LD6A30D010TE ERW6A30830 6LW1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P136209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23374)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A30D010TE ERW6A30830 6LW1H
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2755.0 lumens
Efficiency: N/A
Efficacy: 60.7 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.09
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 45.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P136209

CATALOG NUMBER: LD6A30D010TE ERW6A30830 6LW1H

Luminous Intensity Polar Plot





TEST NUMBER: P136209

CATALOG NUMBER: LD6A30D010TE ERW6A30830 6LW1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83			
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	49	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123885
5°	123573
10°	122405
15°	121549
20°	119089
25°	114593
30°	106100
35°	90356
40°	69197
45°	48863
50°	32986
55°	20883
60°	12174
65°	5573
70°	3453
75°	2269
80°	1127
85°	0



TEST NUMBER: P136209

CATALOG NUMBER: LD6A30D010TE ERW6A30830 6LW1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.8	6.5
10°-20°	506.2	18.4
20°-30°	727.5	26.4
30°-40°	699.7	25.4
40°-50°	416.7	15.1
50°-60°	171.8	6.2
60°-70°	43.2	1.6
70°-80°	9.9	0.4
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1412.5	51.3
0°-40°	2112.2	76.7
0°-60°	2700.7	98.0
0°-90°	2755.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2755.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1899	
5°	1887	179
15°	1800	506
25°	1592	728
35°	1134	700
45°	530	417
55°	184	172
65°	36	43
75°	9	10
85°	0	1
90°	0	



TEST NUMBER: P136209

CATALOG NUMBER: LD6A30D010TE ERW6A30830 6LW1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1898.9
2.5°	1889.9
5°	1886.9
7.5°	1871.8
10°	1847.7
12.5°	1823.7
15°	1799.6
17.5°	1763.5
20°	1715.3
22.5°	1658.2
25°	1591.9
27.5°	1510.7
30°	1408.4
32.5°	1282.0
35°	1134.5
37.5°	975.0
40°	812.5
42.5°	662.1
45°	529.6
47.5°	418.3
50°	325.0
52.5°	249.8
55°	183.6
57.5°	132.4
60°	93.3
62.5°	60.2
65°	36.1
67.5°	24.1
70°	18.1
72.5°	12.0
75°	9.0
77.5°	6.0
80°	3.0
82.5°	3.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)