

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P135493

Luminaire Tested: **LD6A30D010TE ERM6A30930 6LM1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P135493
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23371)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A30D010TE ERM6A30930 6LM1H
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2353.7 lumens
Efficiency: N/A
Efficacy: 51.8 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.9
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 45.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P135493

CATALOG NUMBER: LD6A30D010TE ERM6A30930 6LM1H

Luminous Intensity Polar Plot





TEST NUMBER: P135493

CATALOG NUMBER: LD6A30D010TE ERM6A30930 6LM1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93			
2	108	103	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	81	80			
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74			
5	91	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	54	52			
10	71	61	55	51	70	60	55	51	60	54	51	59	54	51	58	54	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167394
5°	164275
10°	156144
15°	146148
20°	134641
25°	121943
30°	100088
35°	65069
40°	34901
45°	18785
50°	10332
55°	5050
60°	3066
65°	2022
70°	1507
75°	655
80°	977
85°	0



TEST NUMBER: P135493

CATALOG NUMBER: LD6A30D010TE ERM6A30930 6LM1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.6	10.0
10°-20°	605.3	25.7
20°-30°	765.7	32.5
30°-40°	514.7	21.9
40°-50°	169.1	7.2
50°-60°	45.6	1.9
60°-70°	14.2	0.6
70°-80°	4.1	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1605.6	68.2
0°-40°	2120.4	90.1
0°-60°	2335.1	99.2
0°-90°	2353.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2353.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2566	
5°	2508	235
15°	2164	605
25°	1694	766
35°	817	515
45°	204	169
55°	44	46
65°	13	14
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P135493

CATALOG NUMBER: LD6A30D010TE ERM6A30930 6LM1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2565.8
2.5°	2542.2
5°	2508.4
7.5°	2445.7
10°	2357.0
12.5°	2263.0
15°	2163.8
17.5°	2051.6
20°	1939.3
22.5°	1824.5
25°	1694.0
27.5°	1534.8
30°	1328.6
32.5°	1080.6
35°	817.0
37.5°	584.7
40°	409.8
42.5°	287.1
45°	203.6
47.5°	143.5
50°	101.8
52.5°	67.8
55°	44.4
57.5°	31.3
60°	23.5
62.5°	18.3
65°	13.1
67.5°	10.4
70°	7.9
72.5°	5.2
75°	2.6
77.5°	2.6
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)