

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P136213

Luminaire Tested: **LD6A30D010TE ERW6A30930 6LW1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P136213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23374)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A30D010TE ERW6A30930 6LW1H
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2515.3 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.09
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 45.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P136213

CATALOG NUMBER: LD6A30D010TE ERW6A30930 6LW1H

Luminous Intensity Polar Plot





TEST NUMBER: P136213

CATALOG NUMBER: LD6A30D010TE ERW6A30930 6LW1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83			
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	49	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113108
5°	112819
10°	111759
15°	110972
20°	108731
25°	104623
30°	96871
35°	82495
40°	63176
45°	44610
50°	30114
55°	19063
60°	11117
65°	5094
70°	3147
75°	2067
80°	1014
85°	0



TEST NUMBER: P136213

CATALOG NUMBER: LD6A30D010TE ERW6A30930 6LW1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	6.5
10°-20°	462.1	18.4
20°-30°	664.3	26.4
30°-40°	638.8	25.4
40°-50°	380.4	15.1
50°-60°	156.9	6.2
60°-70°	39.5	1.6
70°-80°	9.0	0.4
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1289.6	51.3
0°-40°	1928.4	76.7
0°-60°	2465.7	98.0
0°-90°	2515.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2515.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1734	
5°	1723	163
15°	1643	462
25°	1453	664
35°	1036	639
45°	484	380
55°	168	157
65°	33	39
75°	8	9
85°	0	1
90°	0	



TEST NUMBER: P136213

CATALOG NUMBER: LD6A30D010TE ERW6A30930 6LW1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1733.7
2.5°	1725.5
5°	1722.7
7.5°	1709.0
10°	1687.0
12.5°	1665.0
15°	1643.0
17.5°	1610.1
20°	1566.1
22.5°	1513.9
25°	1453.4
27.5°	1379.3
30°	1285.9
32.5°	1170.5
35°	1035.8
37.5°	890.2
40°	741.8
42.5°	604.5
45°	483.5
47.5°	381.9
50°	296.7
52.5°	228.1
55°	167.6
57.5°	120.9
60°	85.2
62.5°	55.0
65°	33.0
67.5°	22.0
70°	16.5
72.5°	11.0
75°	8.2
77.5°	5.5
80°	2.7
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)